

# Product data sheet

Specifications



## Unity processor - 2 racks (12 slots) / 4 racks (4/6/8 slots) - 930 mA, 5 V DC

TSXP57154M

⚠ Discontinued on: Dec 31, 2018

⚠ To be end-of-service on: Dec 31, 2026

⚠ Discontinued - Service only

**Product availability: Non-Stock - Not normally stocked in  
distribution facility**

### Main

Range Of Product	Modicon Premium Automation platform
Product Or Component Type	Unity processor
Software Designation	Unity Pro

### Complementary

Number Of Racks	2 12 slots 4 4/6/8 slots
Number Of Slots	24 16 32
Discrete I/O Processor Capacity	512 I/O
Analogue I/O Processor Capacity	24 I/O
Number Of Application Specific Channel	8
Integrated Connection Type	Non isolated serial link 2 female mini DIN RS485)19.2 kbit/s) Fipio manager (63 agents) SUB-D 9
Communication Module Processor Capacity	2 1
Memory Description	Internal RAM (with PCMCIA card) 224 kB program Internal RAM (with PCMCIA card) 96 kB data Internal RAM (without PCMCIA card) 96 kB program and data PCMCIA card 256 kB additional data storage
Maximum Size Of Object Areas	32 kB (elementary and derived data) unlocated internal data 4096 %Mi located internal bits 64 %KWi constant words located internal data 64 %MWi internal words located internal data 64 kB (DFB and EFB function blocks) unlocated internal data
Application Structure	1 master task 1 fast task 32 event tasks
Execution Time Per Instruction	0.19 µs Boolean without PCMCIA card 0.25 µs Boolean with PCMCIA card 0.25 µs word or fixed-point arithmetic without PCMCIA card 0.5 µs word or fixed-point arithmetic with PCMCIA card 1.75...2.6 µs floating points with PCMCIA card 1.75...2.6 µs floating points without PCMCIA card
Number Of Instructions Per Ms	2.1 Kinst/ms 65 % Boolean + 35 % fixed arithmetic with PCMCIA card 3.1 Kinst/ms 100 % Boolean with PCMCIA card 3.71 Kinst/ms 65 % Boolean + 35 % fixed arithmetic without PCMCIA card 4.76 Kinst/ms 100 % Boolean without PCMCIA card

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

System Overhead	0.3 ms fast task 1 ms master task
Marking	CE
Local Signalling	for processor running (RUN) 1 LED (green) for activity on Fipio bus (FIP) 1 LED (red) for I/O module or configuration fault (I/O) 1 LED (red) for processor or system fault (ERR) 1 LED (red) for activity on TER or AUX terminal port (TER) 1 LED (yellow)
Current Consumption	930 mA 5 V DC
Module Format	Standard
Net Weight	0.93 lb(US) (0.42 kg)

## Environment

Standards	IEC 61131-2 CSA C22.2 No 213 Class I Division 2 Group C CSA C22.2 No 142 73/23/EEC CSA C22.2 No 213 Class I Division 2 Group A CSA C22.2 No 213 Class I Division 2 Group D 93/68/EEC 92/31/EEC CSA C22.2 No 213 Class I Division 2 Group B UL 508 89/336/EEC
Product Certifications	GL RMRS RINA DNV ABS LR BV
Ambient Air Temperature For Operation	32...140 °F (0...60 °C)
Ambient Air Temperature For Storage	-13...158 °F (-25...70 °C)
Relative Humidity	10...95 % without condensation for operation 5...95 % without condensation for storage
Operating Altitude	0...6561.68 ft (0...2000 m)
Protective Treatment	TC
Ip Degree Of Protection	IP20
Pollution Degree	2

## Ordering and shipping details

Category	US1PC2222558
Discount Schedule	PC22
Gtin	3595863810028
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	10.24 in (26.0 cm)

Package 1 Weight	20.78 oz (589.0 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	17.67 lb(US) (8.015 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### California Proposition 65


WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

---

Dimensions Drawings

Standard and Extendable Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) With screw terminal block modules.
- (2) Maximum depth for all types of modules and their associated connectors.