Product data sheet

Specifications





Switch disconnector, TeSys Control, for ON/OFF, 40A, 4 screws fixing, for mounting for mounting on door

VBF2

Product availability: Stock - Normally stocked in distribution facility

Price*: 237.00 USD

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VBF
Device Application	Preventive maintenance
Product Type	Switch disconnector

Complementary

e emprementar y	
Device Composition	Switch
	Handle
	Tandie
Mounting Support	Handle door
3 11	Switch door
Mounting Method	By 4 screws handle
	·
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Lo] los Potod Operational	
[Ue] lec Rated Operational Voltage	690 V AC 50/60 Hz
-	
lec Rated Operational Power In W	11 kW 690 V AC-3)
	15 kW 690 V AC-23A)
	11 kW 400415 V AC-3)
	15 kW 500 V AC-3)
	18.5 kW 500 V AC-23A)
	5.5 kW 230240 V AC-3)
	7.5 kW 230240 V AC-23A)
	15 kW 400415 V AC-23A)
[Ie] Rated Operational Current	29 A AC-23 Ue: 400 V
[Ith] Conventional Free Air	40 A
Thermal Current	
[Ithe] Conventional Enclosed	32 A
Thermal Current	
Making Capacity (I Rms)	400 A 400 V AC-21A
	400 A 400 V AC-21A 400 A 400 V AC-22A
	400 A 400 V AC-23A
Breaking Capacity	320 A 400 V AC-21A)
	320 A 400 V AC-22 A)
	,
	320 A 400 V AC-23A)
Rated Conditional Short Circuit	10 kA 400 V 50 A aM
Current	
	10 kA 400 V 50 A gG

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	480 A 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 KV
Suitability For Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Color	Black
Handle Front Plate Color	Black
Rotary Handle Padlocking	1 to 3 padlocks 0.160.31 in (48 mm)
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-15
lec Terminal Connection	Power circuit screw clamp terminals 0.02 in² (10 mm²) solid Power circuit screw clamp terminals 0.01 in² (6 mm²) flexible - with cable end
Tightening Torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Base Dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Product Weight	0.55 lb(US) (0.25 kg)

Environment

Standards	IEC 60947-3
Product Certifications	CCC
	GL
	CSA
	UL
	UKCA
Degree Of Protection	IP20 conforming to IEC 60529
C C	IP65
Protective Treatment	TC
Mechanical Robustness	Vibrations 10150 Hz 1 gn) IEC 60068-2-6
	Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature For	-4…122 °F (-20…50 °C)
Operation	
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	Main switch disconnector

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
Gtin	3389110449372
Returnability	No

Packing Units

r adning offics	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	4.72 in (12.000 cm)
Package 1 Weight	7.69 oz (218.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	12.37 lb(US) (5.611 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	116.60 lb(US) (52.888 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov