

# Product data sheet

Specifications



Connector module, Lexium 32i,  
connection for industrial connectors,  
CANopen, 4 DI sink

VW3M9202

Product availability: Non-Stock - Not normally stocked in  
distribution facility

Price\*: 213.34 USD

## Main

Range Of Product	Lexium 32i
Product Or Component Type	Connector module
Accessory / Separate Part Category	Connection accessories
Electrical Connection	Industrial connector

## Complementary

Product Compatibility	Drive control unit LXM32i CANopen
Accessory / Separate Part Destination	Motor BMI with drive control unit Lexium 32i
Range Compatibility	Lexium 32i
Communication Interface	CANmotion CANopen DS402
Input/Output Type	4 discrete inputs
Discrete Input Logic	Sink
Net Weight	0.48 lb(US) (0.218 kg)

## Ordering and shipping details

Category	US1PC5618289
Discount Schedule	PC56
Gtin	3606480610899
Returnability	No
Country Of Origin	DE

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.23 in (8.2 cm)
Package 1 Width	4.53 in (11.5 cm)
Package 1 Length	6.69 in (17.0 cm)
Package 1 Weight	7.69 oz (218.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	12

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.34 lb(US) (3.329 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

 Mercury Free

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile


[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Connections and Schema

Connection of I/O Module for CANopen with Industrial Connectors



- (1) IN  
(2) OUT

Signal	Meaning
+24VDC	24 V signal power supply
0VDC	Reference potential to +24VDC
DI0	Digital input 0
DI1	Digital input 1
DI2	Digital input 2
DI3	Digital input 3
STO_A	Safety function STO
STO_COM	Reference potential for safety function STO
STO_B	Safety function STO
SHLD	Shield (grounded internally)
CAN_0V	Reference potential for CAN
CAN_H	CAN interface
CAN_L	CAN interface

Signal	Meaning
NC	Not connected