

Product data sheet

Specifications



Additional pole,TeSys Control, 12A,for V02

VZ02

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 31.50 USD

Main

Range	TeSys
Device Short Name	VZ
Product Or Component Type	Additional pole
Performance Level	High performance
Poles Description	1P
Contacts Type And Composition	1 NO
Product Compatibility	V02
Range Compatibility	TeSys TeSys VARIO switch disconnecter
Network Type	DC AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes

Complementary

Mounting Location	Left Right
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	12 A
[Ithe] Conventional Enclosed Thermal Current	10 A
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-1...5
Connections - Terminals	Power circuit screw clamp terminals 0.01 in² (6 mm²) flexible - with cable end Power circuit screw clamp terminals 0.02 in² (10 mm²) solid
Tightening Torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Height	2.91 in (74 mm)
Width	0.63 in (16 mm)
Depth	1.38 in (35 mm)
Net Weight	0.11 lb(US) (0.05 kg)

Environment

Standards	IEC 60947-3
-----------	-------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CSA UL GL UKCA
Protective Treatment	TC
Ip Degree Of Protection	IP20 conforming to IEC 60529
Mechanical Robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature For Operation	-4...122 °F (-20...50 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
Gtin	3389110448856
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	1.46 in (3.7 cm)
Package 1 Weight	1.62 oz (46.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	69
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.77 lb(US) (3.524 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓

Toxic Heavy Metal Free

✓

Mercury Free

✓

Rohs Exemption Information

Yes

✓

Pvc Free

✓

Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations