Product datasheet

Specifications





Spacial S3HF H1000xW800xD300 EMC-immunity IP55 RAL7035

NSYS3HF10830P

Main

Range	Spacial
Product Name	Spacial S3HF
Application	Industrial application
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	300 mm
Door Type	Plain
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door with lock 1 mounting plate

Complementary

Body Type	Single piece body
Number Of Doors	Front face: 1 door(s)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body: aluzinc
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 60529
Net Weight	51.7 kg

Environment

Electromagnetic Compatibility	EMC immunity
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP55

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	100.0 cm
Package 1 Width	80.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	51.7 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations