# **Product datasheet**

Specification





motion control stepper motor drive - SD328 - Profibus DP fieldbus - <= 6.8 A

SD328BU68S2

#### Main

Range Of Product	Lexium SD3	
Product Or Component Type	Motion stepper drive	
Device Short Name	SD328	
Supply Voltage Limits	200240 V 100120 V	
Bus Type	Fieldbus	

## Complementary

Format Of The Drive	Block	
Network Number Of Phases	Single phase	
[Us] Rated Supply Voltage	100120 V - 1510 % 200230 V - 1510 %	
Supply Voltage Type	AC/DC	
Network Frequency Limits	5060 Hz (- 1510 %)	
Communication Interface	Profibus DP fieldbus, integrated	
Maximum Motor Phase Current	6.8 A	
Current Consumption	5 A 230 V main supply 7 A 115 V main supply <= 0.2 mA 24 V control voltage	
Nominal Power	280 W at 115 V 420 W at 230 V	
Short-Circuit Current	0.5 kA	
Power Losses	<= 65 W	
Associated Fuse Rating	ting 10 A at 115 V 6 A at 230 V	
Overvoltage Category	III	
Inrush Current	60 A	
Maximum Leakage Current	30 mA <10 m IEC 60990-3	
Voltage State 0 Guaranteed	State 0 Guaranteed -35 V for 24 V input signals	
Voltage State 1 Guaranteed	1530 V for 24 V input signals	
Input Current	10 mA for 24 V input signals	
Maximum Input Frequency	200 kHz for signal input ENC_A, ENC_B, ENC_I - control type pulse/direction 400 kHz for signal input ENC_A, ENC_B, ENC_I - control type A/B	
Maximum Output Frequency	400 kHz for pulse/direction interface A/B 200 kHz for pulse/direction interface pulse/direction	

Maximum Switching Current 50 mA (24 V output signals)		
Maximum Voltage Drop	<1 V 50 mA load for 24 V output signals	
Physical Interface	RS422 - pulse/direction interface RS422 - signal input ENC_A, ENC_B, ENC_I	
Output Voltage	<= 30 V (24 V output signals) 4.755.25 V (ENC+5V_OUT signal output)	
Input Voltage	24 V -15 %/+20 % for 24 V control voltage	
Residual Ripple	< 5 % (24 V control voltage)	
Resistance	5 kOhm (pulse/direction interface)	
Safety Function	Safe torque off safety function for machine conforming to IEC/EN 61800-5-2 Safe torque off safety function for machine conforming to ISO 13849-1 level d Safe torque off safety function for system process conforming to EN/IEC 61508 lev SIL2 Safe torque off safety function for system process conforming to IEC/EN 61800-5-2	
Type Of Cooling	Fan	
Maximum Mechanical Speed	3000 rpm	
Height	145 mm	
Width	72 mm	
Depth	140 mm	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Net Weight	1.2 kg	

## **Environment**

Electromagnetic Compatibility	Electrostatic discharge level 3 conforming to IEC 61000-4-2 Immunity to electrical transients level 4 conforming to IEC 61000-4-4 Immunity to radiated radio-electrical interference level 3 conforming to IEC 61000-4-3 Voltage/current impulse level 3 conforming to IEC 61000-4-5	
Standards	EN/IEC 61800-3 EN/IEC 61800-5-1	
Product Certifications  UL  cUL  TÜV		
Marking	CE	
Ambient Air Temperature For Operation	050 °C	
Ambient Air Temperature For Storage	-2570 °C	
Pollution Degree	Level 2	
relative Humidity 585 % without condensation		
> 1000 m without derating > 1000< 2000 m without derating (maximum ambient temperature 40°C, no protective film, lateral distance of > 50mm)		
Vibration Resistance	1 gn (f= 13150 Hz) conforming to IEC 60068-2-6 1.5 mm (f= 313 Hz) conforming to IEC 60068-2-6	
Ip Degree Of Protection	IP20 On upper part: IP40 (without removal of protective film)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm

Package 1 Width	18 cm
Package 1 Length	19.5 cm
Package 1 Weight	1.34 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9.292 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance


<b>②</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	

#### **Certifications & Standards**


Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope)	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

#### **Dimensions Drawings**

#### **Dimensions**




#### EMC mounting plate (included)



### SD328BU68S2

### Mounting and Clearance

#### **Mounting and Clearance**




Ambient	Mounting	Mounting recommendations		
temperature	distances	Without protective film (1)	With protective film	
	d > 50 mm/ 1.97 in.	None	None	
0 +40 °C	d > 50 mm/ 1.97 in.	None	d > 10 mm/0.39 in.	
d > 50 mm/ 1.97 in. None +40 +50 °C d > 50 mm/ 1.97 in. Reduce nominal and continuous current	1	None	Reduce nominal and continuous current by 2.2 % per °C above 40 °C	
	1	Operation not possible		


<sup>(1)</sup> Recommendation: remove protective film after installation.

Connections and Schema

#### SD328B Connection Example with Fieldbus Control



#### **Example of Application of the Safety Function: Category 0 Stop**



#### **Example of Application of the Safety Function: Category 1 Stop**

