## **Product data sheet**

Specifications





Manual overload reset push button, Harmony XB4, black flush pushbutton Ø22 mm for 16...26 mm actuation distance

XB4BA822



(!) Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony XB4	
Product Or Component Type	Manual overload reset push-button	
Device Short Name	XB4	
Bezel Material	Chromium plated metal	
Fixing Collar Material	Zamak	
Head Type	Standard	
Mounting Diameter	0.89 in (22.5 mm)	
Operator Profile	Black flush, unmarked	
Activating Distance	0.631.02 in (1626 mm)	

### Complementary

Net Weight	0.08 lb(US) (0.038 kg)
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
Shape Of Signaling Unit Head	Round
Operating Travel	0.39 in (10 mm)
Mechanical Durability	5000000 cycles

#### **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I IEC 60536
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 13 NEMA 4X
Ik Degree Of Protection	IK03 conforming to IEC 50102

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	JIS C8201-5-1 IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-4 IEC 60947-1 UL 508 IEC 60947-5-5 JIS C8201-1
Product Certifications	GL LROS (Lloyds register of shipping) CSA UL Listed DNV BV

## Ordering and shipping details

Category	US10CS222468
Discount Schedule	0CS2
Gtin	3389110102055
Returnability	No
Country Of Origin	FR

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.72 in (12.0 cm)
Package 1 Width	1.38 in (3.5 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	1.31 oz (37.0 g)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance




#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Dimensions Drawings**

#### **Dimensions**



e: panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

#### Mounting and Clearance

# Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board

Connection by Faston Connectors

(1)

(2)

(3)

(4)

- (1) Diameter on finished panel or support
- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm  $_0^{+0.4}$  / 0.88 in.  $_0^{+0.016}$ )
- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.