

Product data sheet

Specifications



Preventa safety PLC compact - SIL 3 - 20 I not isolated

XPSMF31222

⚠ Discontinued on: Dec 2, 2020

⚠ To be end-of-service on: Dec 31, 2027

⚠ Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety PLC compact
Safety Module Name	XPSMF31
Safety Module Application	For numerous machine safety functions and for the protection of personnel
Safety Use Category	Category 4 EN 954-1/ISO 13849-1 SIL 3 IEC 61508
Structure Type	10BASE-T/100BASE-TX, Modbus TCP/IP 10BASE-T/100BASE-TX, safe Ethernet

Complementary

Function Of Module	Monitoring safety actuators discrete output Monitoring safety detection discrete input Monitoring safety dialogue discrete input Monitoring safety dialogue discrete output
[Us] Rated Supply Voltage	24 V DC - 15...20 %
No Load Current	0.4 A
Protection Type	Internal fuse
Clock	With, supplied by backup capacitor for 1 week following loss of supply
Response Time	Depending on size of application
Memory Description	User logic 250 kB application User logic 250 kB data
Discrete Input Number	20 not isolated
Voltage State 0 Guaranteed	<= 5 V discrete input
Voltage State 1 Guaranteed	>= 15 V discrete input
Current State 0 Guaranteed	1...1.5 mA discrete input)
Current State 1 Guaranteed	>= 2 mA discrete input)
Discrete Input Voltage	20 V
Discrete Input Current	100 mA
Input Protection Type	Protected against short-circuit to earth Protected against short-circuit
Input Overvoltage Protection	500 V discrete input IEC 61000-4-5
Switching Voltage	7.5 V
Discrete Output Number	8

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discrete Output Voltage	24 V DC
Output Voltage Tolerance	+/- 2%
Discrete Output Current	1 A 140 °F (60 °C) channels 4 and 8) 2 A 122 °F (50 °C) channels 4 and 8) 0.5 A 140 °F (60 °C) channels 1 to 3 and 5 to 7) <= 7 mA all channels)
Minimum Load	2 mA per discrete output
Maximum Leakage Current	1 mA 2 V at state 0 discrete output
Overload Protection	Shutdown of outputs concerned with cyclic reconnection
Communication Port Protocol	Safe Ethernet 4 RJ45 100 Mbps dual twisted pair cable
Exchange Mode	Half duplex, full duplex, autonegotiation Modbus TCP/IP Half duplex, full duplex, autonegotiation safe Ethernet
Method Of Access	Slave Modbus TCP/IP
Concept	Transparent Ready, Modbus TCP/IP
Web Server	Class A10, Modbus TCP/IP
Web Services	Modbus identification request, Modbus TCP/IP Modbus TCP/IP messaging (reading/writing of data words), Modbus TCP/IP Modbus TCP/IP server, Modbus TCP/IP Standard 502, Modbus TCP/IP
Operating Distance	<= 100 m between station) discrete input <= 100 m between station) discrete output
Number Of Terminal Blocks	1 power supply 2 discrete output 5 discrete input
Connections - Terminals	Discrete input/output circuit captive screw clamp terminals, 2 x 0.5 mm ² AWG 20) flexible with cable end Discrete input/output circuit captive screw clamp terminals, 1 x 0.14...1 x 1.5 mm ² AWG 28...AWG 16) flexible without cable end Discrete input/output circuit captive screw clamp terminals, 1 x 0.14...1 x 1.5 mm ² AWG 28...AWG 16) solid without cable end Power supply captive screw clamp terminals, 1 x 0.2...1 x 2.5 mm ² AWG 24...AWG 12) flexible without cable end Power supply captive screw clamp terminals, 1 x 0.2...1 x 2.5 mm ² AWG 24...AWG 12) solid without cable end Discrete input/output circuit captive screw clamp terminals, 1 x 0.25...1 x 0.5 mm ² AWG 22...AWG 20) flexible with cable end Discrete input/output circuit captive screw clamp terminals, 1 x 0.25...1 x 1.5 mm ² AWG 22...AWG 16) flexible without cable end Power supply captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm ² AWG 22...AWG 16) flexible with cable end Power supply captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm ² AWG 22...AWG 16) flexible without cable end Discrete input/output circuit captive screw clamp terminals, 2 x 0.14...2 x 0.5 mm ² AWG 28...AWG 20) solid without cable end Discrete input/output circuit captive screw clamp terminals, 2 x 0.14...2 x 0.75 mm ² AWG 28...AWG 18) flexible without cable end Power supply captive screw clamp terminals, 2 x 0.2...2 x 1.5 mm ² AWG 24...AWG 12) flexible without cable end Power supply captive screw clamp terminals, 2 x 0.2...2 x 1.5 mm ² AWG 24...AWG 12) solid without cable end Discrete input/output circuit captive screw clamp terminals, 2 x 0.25...2 x 0.34 mm ² AWG 22) flexible without cable end Power supply captive screw clamp terminals, 2 x 0.25...2 x 1 mm ² AWG 22...AWG 18) flexible without cable end Power supply captive screw clamp terminals, 2 x 0.5...2 x 1.5 mm ² AWG 22...AWG 16) flexible with cable end
Tightening Torque	1.95...2.21 lbf.in (0.22...0.25 N.m)
Wire Stripping Length	0.35 in (9 mm)
Current Consumption	8 A 24 V DC on power supply
Mounting Support	35 mm symmetrical DIN rail
Depth	2.62 in (66.5 mm)

Height	4.45 in (113 mm)
Width	9.96 in (253 mm)
Net Weight	2.20 lb(US) (1 kg)

Environment

Standards	IEC 61131 DIN V 19250 EN 50156 pending DIN V 0801
Immunity To Microbreaks	10 ms
Ip Degree Of Protection	IP20 enclosure)
Ambient Air Temperature For Operation	32...140 °F (0...60 °C) EN 61131-2
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C) EN 61131-2
Relative Humidity	95 % supply not connected
Operating Altitude	< 6561.68 ft (2000 m)
Pollution Degree	2
Electrical Shock Protection Class	Class II EN/IEC 61131-2
Electromagnetic Compatibility	EN/IEC 61131-2
Vibration Resistance	1 gn 10...150 Hz)EN 61131-2
Shock Resistance	15 gn 11 ms EN 61131-2
Resistance To Electrostatic Discharge	4 kV contact EN/IEC 61000-4-2 8 kV on air EN/IEC 61000-4-2
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 26...1000 MHz EN/IEC 61000-4-3

Ordering and shipping details

Category	22478 - XPS SAFETY PLC
Discount Schedule	SAF1
Gtin	3389119010634
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.10 in (15.5 cm)
Package 1 Width	7.28 in (18.5 cm)
Package 1 Length	11.61 in (29.5 cm)
Package 1 Weight	3.67 lb(US) (1.664 kg)
Unit Type Of Package 2	S04
Number Of Units In Package 2	3
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)

Package 2 Weight	14.46 lb(US) (6.559 kg)
------------------	-------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)


Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov

Presentation


Housing Elements

Front View




No.	Description
1	power supply input
2	digital outputs
3	digital inputs
4	indicators

Top View




Bottom View




Dimensions Drawings

Dimensions

Front View




Side View




Mounting and Clearance

Mounting

Minimum Clearances




Air Circulation



No.	Description
1	The height of the cable ducts is less than 40 mm / 1.57 in.
2	The height of the cable ducts is greater than 40 mm / 1.57 in.

L = H - 40 mm / 1.57 in.
L = length of the spacer
H = height of the cable duct
Minimum clearance when H > 40 mm/1.57 in. and no spacer




Mounting Precautions Relating to Connectors

Access to Modbus Serial Link (RTU)

SUB-D 9-pin connector


mm
in.



(1) minimum value

Adaptor XPS MFADAPT


mm
in.




(1) minimum value

Access to PROFIBUS DP

mm
in.



Access to Ethernet Network




(1) minimum value

Connections and Schema

Wiring Diagrams

Emergency Stop Connections (Line Control)



Actuator Connections to the Outputs

