Bảng thông số sản phẩm

Thông số kỹ thuật





Contactor, TeSys Deca, 3P(3NO), AC-3/AC-3e, 440V, 95A, 24V DC standard coil, screw clamp terminals

LC1D95BD

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-3e AC-4 AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz
[le] Rated Operational Current	95 A (at <60 °C) at <= 440 V AC-3 for power circuit 125 A (at <60 °C) at <= 690 V AC-1 for power circuit 95 A (at <60 °C) at <= 440 V AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

Motor Power Kw	25 kW at 220230 V AC 50 Hz (AC-3) 45 kW at 380400 V AC 50 Hz (AC-3)	
	45 kW at 415440 V AC 50 Hz (AC-3)	
	55 kW at 500 V AC 50 Hz (AC-3)	
	45 kW at 660690 V AC 50 Hz (AC-3)	
	15 kW at 400 V AC 50 Hz (AC-4)	
	25 kW at 220230 V AC 50 Hz (AC-3e)	
	45 kW at 380400 V AC 50 Hz (AC-3e)	
	45 kW at 415440 V AC 50 Hz (AC-3e)	
	55 kW at 500 V AC 50 Hz (AC-3e)	
	45 kW at 660690 V AC 50 Hz (AC-3e)	
Motor Power Hp	7.5 hp at 120 V AC 60 Hz for 1 phase motors	
	15 hp at 230/240 V AC 60 Hz for 1 phase motors	
	30 hp at 200/208 V AC 60 Hz for 3 phases motors	
	30 hp at 230/240 V AC 60 Hz for 3 phases motors	
	60 hp at 460/480 V AC 60 Hz for 3 phases motors	
	60 hp at 575/600 V AC 60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	125 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	1100 A at 440 V AC for power circuit conforming to IEC 60947	
	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	

3 thg 5, 2024 Life Is On Schneider

Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947	
[Icw] Rated Short-Time Withstand Current	1100 A 40 °C - 1 s for power circuit 800 A 40 °C - 10 s for power circuit 400 A 40 °C - 1 min for power circuit 135 A 40 °C - 10 min for power circuit 140 A - 100 ms for signalling circuit 120 A - 500 ms for signalling circuit 100 A - 1 s for signalling circuit	
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 200 A gG at <= 690 V coordination type 1 for power circuit 160 A gG at <= 690 V coordination type 2 for power circuit	
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit	
Power Dissipation Per Pole	12.5 W AC-1 7.2 W AC-3 7.2 W AC-3e	
[Ui] Rated Insulation Voltage	Power circuit: 1000 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1	
Overvoltage Category	III	
Pollution Degree	3	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947	
Safety Reliability Level	B10d = 1.3 Mcycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20 Mcycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	10 Mcycles	
Electrical Durability	1.2 Mcycles 95 A AC-3 1.3 Mcycles 125 A AC-1 1.2 Mcycles 95 A AC-3e	
Control Circuit Type	DC standard	
Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC 0.851.1 Uc (-4055 °C):operational DC 11.1 Uc (5570 °C):operational DC	
Inrush Power In W	22 W (at 20 °C)	
Hold-In Power Consumption In W	22 W at 20 °C	
Operating Time	95130 ms closing 2035 ms opening	
Time Constant	75 ms	
Maximum Operating Rate	3600 cyc/h 60 °C	
Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: connector 1 450 mm² - cable stiffness: flexible without cable end Power circuit: connector 2 425 mm² - cable stiffness: flexible with cable end Power circuit: connector 2 416 mm² - cable stiffness: flexible with cable end Power circuit: connector 1 450 mm² - cable stiffness: solid without cable end Power circuit: connector 2 416 mm² - cable stiffness: solid without cable end Power circuit: connector 2 425 mm² - cable stiffness: solid without cable end	

Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 12 N.m - on connector - with screwdriver flat Ø 6 to Ø 8 mm Power circuit: 12 N.m - on connector hexagonal screw head 4 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2	
1 NO + 1 NC	
type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
25400 Hz	
17 V for signalling circuit	
5 mA for signalling circuit	
> 10 MOhm for signalling circuit	
1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Rail Plate	
EN/IEC 60947-1 EN/IEC 60947-4-1 EN/IEC 60947-5-1 GB/T 14048.4	
IECEE CB Scheme CCC EAC LROS (Lloyds register of shipping) RINA BV DNV-GL	
IP20 front face conforming to IEC 60529	
TH conforming to IEC 60068-2-30	
conforming to IACS E10 exposure to damp heat	
-4060 °C 6070 °C with derating	
03000 m	
850 °C conforming to IEC 60695-2-1	
V1 conforming to UL 94	
Vibrations contactor open (2 Gn, 5300 Hz) Shocks contactor open (8 Gn for 11 ms) Vibrations contactor closed (3 Gn, 5300 Hz) Shocks contactor closed (10 Gn for 11 ms)	
127 mm	
85 mm	
186 mm	
2.61 kg	
PCE	
1	
11.000 cm	
16.300 cm	

Package 1 Length	21.700 cm
Package 1 Weight	2.566 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.445 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	97.892 kg

Contractual warranty

Warranty 18 months



Nhãn **Green PremiumTM** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO_2 thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

Tìm hiểu thêm về Green Premium >

Hướng dẫn đánh giá về sự bền vững của sản phẩm >





Minh bach RoHS/REACh

Hiệu suất sức khoẻ

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Pvc Free	

Chứng nhận & Tiêu chuẩn


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Bảng thông số sản phẩm

LC1D95BD

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D80 and D95
а		85
b1	with LAD 4BB3	_
	with LA4 DF, DT	_
c	without cover or add-on blocks	181
C	with cover, without add-on blocks	186
c1	with LAD N (1 contact)	204
	with LAD N or C (2 or 4 contacts)	210
c2	with LA6 DK10	221
с3	with LAD T, R, S	229
	with LAD T, R, S and sealing cover	233

Bảng thông số sản phẩm

LC1D95BD

Connections and Schema

Wiring

