

Bảng thông số sản phẩm

Thông số kỹ thuật



TeSys LRF - electronic thermal overload relay - 132...220 A - class 20

LR9F5571

⚠ Ngừng sản xuất vào: 10 thg 7, 2021

⚠ Ngừng sản xuất

Main

Range	TeSys
Product Name	TeSys LRF
Device Short Name	LR9F
Product Or Component Type	Electronic thermal overload relay
Relay Application	Motor protection
Product Compatibility	LC1F185...LC1F265
Network Type	AC
Thermal Overload Class	Class 20 conforming to IEC 60947-4
Thermal Protection Adjustment Range	132...220 A

Complementary

Network Frequency	50/60 Hz
Mounting Support	Direct on contactor Plate
Tripping Threshold	1.12 +/- 0.06 In tripping conforming to IEC 60947-4-1
Surge Withstand	4 kV conforming to IEC 61000-4-5
Contacts Type And Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for control circuit
[Ue] Rated Operational Voltage	1000 V AC 50/60 Hz for power circuit conforming to VDE 0110 group C
[Ui] Rated Insulation Voltage	Power circuit: 1000 V AC conforming to IEC 60947-4
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-1
Phase Failure Sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Reset	Manual reset on front relay
Control Type	Dial white full-load current adjustment Test button red Push-button reset Push-button red stop
Local Signalling	Trip indicator
Temperature Compensation	-20...70 °C
Current Consumption	<= 5 mA no-load
Switching Capacity For Alarm	0...150 mA
Maximum Voltage Drop	<2.5 V closed state

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Connections - Terminals	Control circuit: screw clamp terminals 1 cable 0.75...2.5 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable 0.75...2.5 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 1 cable 0.75...4 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 1...1.5 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 1...2.5 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 1 mm ² - cable stiffness: solid Power circuit: lugs-ring terminals M10
Tightening Torque	Control circuit: 1.2 N.m on screw clamp terminals Power circuit: 35 N.m on screw clamp terminals
Height	101 mm
Width	115 mm
Depth	123.5 mm
Net Weight	0.95 kg

Environment

Standards	IEC 60255-8 EN 60947-4-1 IEC 60255-17 IEC 60947-4-1 VDE 0660
Product Certifications	CSA UL UKCA
Protective Treatment	TH
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-20...55 °C conforming to IEC 60255-8
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	<= 2000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations 5...300 Hz: 2 GN conforming to IEC 60068-2-6
Dielectric Strength	6 kV 50 Hz conforming to IEC 255-5
Electromagnetic Compatibility	Resistance to electrostatic discharge: 6 kV in indirect mode conforming to IEC 61000-4-2 Resistance to electrostatic discharge: 8 kV in air conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test: 10 V/m conforming to IEC 61000-4-3 Fast transients immunity test: 2 kV conforming to IEC 61000-4-4

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	15.0 cm
Package 1 Length	16.0 cm
Package 1 Weight	1.02 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	11

Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	12.1 kg

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information