

Product data sheet

Specifications



green flush/red projecting double-headed pushbutton Ø22 unmarked

ZB4BL93347

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Main

Range Of Product	Harmony XB4
Product Or Component Type	Head for double-headed push-button
Device Short Name	ZB4
Bezel Material	Black metal
Mounting Diameter	0.87 in (22 mm)
Sale Per Indivisible Quantity	1
Shape Of Signaling Unit Head	Rectangular
Type Of Operator	spring return
Operator Profile	1 flush - 1 projecting push-buttons
Operators Description	Green unmarked - red unmarked

Complementary

Cad Overall Width	1.18 in (30 mm)
Cad Overall Height	1.97 in (50 mm)
Cad Overall Depth	1.38 in (35 mm)
Net Weight	0.11 lb(US) (0.051 kg)
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
Colour Of Marking	White marking when green, red or black caps Black marking when white caps
Operator Profile	Green flush, unmarked Red projecting, unmarked
Mechanical Durability	1000000 cycles

Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Electrical Shock Protection Class	Class I IEC 60536
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 13 NEMA 4X
Ik Degree Of Protection	IK03 conforming to IEC 50102

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508
	CSA C22.2 No 14
	EN/IEC 60947-5-5
	EN/IEC 60947-5-1
	EN/IEC 60947-1
	EN/IEC 60947-5-4
	JIS C8201-5-1
	JIS C8201-1
Product Certifications	CSA
	BV
	UL Listed
	GL
	DNV
LROS (Lloyds register of shipping)	
Vibration Resistance	5 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27
	50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Gtin	3389110823615
------	---------------

Contractual warranty

Warranty	18 months
----------	-----------