Bảng thông số sản phẩm

Thông số kỹ thuật





3-phase control relay, Harmony Control Relays, 5A, 2NO, phase failure detection, 24..240V AC DC

RM35TM50MW

Main

Range Of Product	Harmony Control Relays
Relay Type	Motor temperature control relay
Product Or Component Type	Motor temperature control relay
Product Specific Application	For 3-phase supply
Relay Name	RM35TM
Relay Monitored Parameters	Phase sequence Motor temperature via PTC probe Phase failure detection
Time Delay	Without
Switching Capacity In Va	1250 VA
Measurement Range	208480 V AC 153100 Ohm
Contacts Type And Composition	2 NO
[Uc] Control Circuit Voltage	24240 V

Complementary

J	
Reset Time	10000 ms output
Maximum Switching Voltage	250 V AC 250 V DC
Minimum Switching Current	10 mA at 5 V DC
Maximum Switching Current	5 A AC 5 A DC
[Un] Rated Nominal Voltage	24240 V AC/DC 50/60 Hz, non self-powered
Supply Voltage Limits	20.4264 V AC 20.4264 V DC
Power Consumption In Va	04 VA at 24240 V AC
Power Consumption	0.5 W DC
Control Circuit Frequency	5060 Hz +/- 10 %
Resistance Across Terminals	602 mOhm
Output Contacts	2 NO
Nominal Output Current	5 A
Measurement Voltage Limits	176528 V AC
Delay At Power Up	500 ms
Voltage Range	176528 V

Response Time	> 50 ms (input Y1 (contact Y1-T1) and push-button)
[Uc] Control Circuit Voltage	<= 3.6 V of temperature control circuit (T1-T2 terminals open)
Short-Circuit Current	0.007 A temperature sensing circuit (T1-T2 terminals short circuited)
Maximum Resistance	1500 Ohm for temperature sensor at 20 °C
Fripping Threshold	3100 Ohm +/- 10 % for temperature control circuit
Reset Threshold	1650 Ohm +/- 10 % for temperature control circuit
Marking	CE
Overvoltage Category	III conforming to IEC 60664-1
Insulation Resistance	> 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60255-5 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC 60664-1 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60255-5 > 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60664-1 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC 60255-5 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60664-1
Ui] Rated Insulation Voltage	400 V conforming to IEC 60664-1
Supply Frequency	50/60 Hz +/- 10 %
Operating Position	Any position without derating
Connections - Terminals	Screw terminals, 1 x 0.51 x 4 mm² (AWG 20AWG 11) solid without cable end Screw terminals, 2 x 0.52 x 2.5 mm² (AWG 20AWG 14) solid without cable end Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 24AWG 12) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) flexible with cable end
Fightening Torque	0.61 N.m conforming to IEC 60947-1
Housing Material	Self-extinguishing plastic
ocal Signalling	LED (green) for power ON LED (yellow) for phase of relay (R2) LED (yellow) for temperature of relay (R1)
Mounting Support	35 mm symmetrical DIN rail conforming to IEC 60715
Electrical Durability	10000 cycles
Mechanical Durability	30000000 cycles
Operating Rate	<= 360 operations/hour full load
Utilisation Category	AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
Width	35 mm
Net Weight	0.13 kg

Environment

Immunity To Microbreaks	20 ms at 20.4 V
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4
	Emission standard for residential, commercial and light-industrial environments
	conforming to IEC 61000-6-3
	Immunity for industrial environments conforming to IEC 61000-6-2

Standards	IEC 60255-6 IEC 60034-11-2
Product Certifications	GL UL GOST C-Tick CSA
Directives	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2050 °C
Relative Humidity	95 % at 55 °C conforming to IEC 60068-2-30
Vibration Resistance	0.35 mm (f= 557.6 Hz) conforming to IEC 60068-2-6 1 gn (f= 57.6150 Hz) conforming to IEC 60255-21-1
Shock Resistance	15 gn for 11 ms conforming to IEC 60255-21-1
Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529 IP30 (casing) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Dielectric Test Voltage	2 kV, 1 min AC 50 Hz
Non-Dissipating Shock Wave	4 kV

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	7.8 cm
Package 1 Length	9.6 cm
Package 1 Weight	131.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	48
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.0 kg

Contractual warranty

Warranty 18 months



Nhãn **Green PremiumTM** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO_2 thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

Tìm hiểu thêm về Green Premium >

Hướng dẫn đánh giá về sự bền vững của sản phẩm >





Minh bach RoHS/REACh

Hiệu suất sức khoẻ



Mercury Free



Rohs Exemption Information

Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Bảng thông số sản phẩm


RM35TM50MW

Dimensions Drawings

3-Phase Supply and Motor Temperature Control Relays

Dimensions and Mounting






Bảng thông số sản phẩm

RM35TM50MW

Connections and Schema

3-Phase Supply and Motor Temperature Control Relays

Wiring Diagram




Bảng thông số sản phẩm

RM35TM50MW


Technical Description

Function Diagrams

Phase Sequence Control and Phase Failure Detection (U measured < 0.7 x nominal supply voltage)



Motor Temperature Control via PTC Probe



Legend

Un Nominal 3-phase supply voltage R T1-T2 Resistance between terminals T1 and T2 11-14 R1 output relay connections Relay status: black color = energized.

NOTE: The temperature control relay can take up to 6 PTC (positive temperature coefficient) probes wired in series between terminals T1 and T2.