

Bảng thông số sản phẩm

Thông số kỹ thuật



SE BACK-UPS 650VA, 230V,
AVR, IEC Sockets replace by
BXS750MI

SX3650CI

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	390 W
Rated Power In Va	650 VA
Output Connection Type	4 IEC 60320 C13 1 IEC Jumpers
Cable Length	1.16 m
Battery Type	Lead-acid battery

Batteries & Runtime

Thời Gian Chạy	View Runtime Graph
Hiệu Suất	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	8 h
Battery Charger Power	10 W rated
Battery Life	3...5 year(s)
Replacement Battery	APCRBC110
Extended Runtime	0

General

Provided Equipment	user manual
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	20 cm

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Width	11.5 cm
Depth	25.7 cm
Net Weight	6.2 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	45...65 Hz
Input Voltage Limits	140...300 V
Maximum Input Current	7 A
Switching Current Capacity	7 A

Output

Maximum Configurable Power In W	390 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Maximum Configurable Power In Va	650 VA
Transfer Time	6 ms typical : 10 ms maximum

Conformance

Product Certifications	CE GOST NEMKO
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...9144.00 m
Acoustic Level	45 dBA

Communications & Management

Control Panel	LED Status display with on line : on battery
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge Energy Rate	273 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27 cm
Package 1 Width	19.8 cm
Package 1 Length	34 cm
Package 1 Weight	7 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	10
Package 2 Height	80 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	72 kg
Scc14	60731304307435

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Sử dụng hiệu quả năng lượng Take-back Minh bạch RoHS/REACH

Hiệu suất tài nguyên

- ✓

Energy Efficient Product
- ✓

Take-Back Program Available

Hiệu suất sức khỏe

- ✓

Rohs Exemption Information

Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information