Specifications





Head for non illuminated pushbutton, Harmony XB5, plastic, blue, mushroom 40mm, 22mm, spring return

ZB5AC6

() Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony XB5 |
|-------------------------------|--------------------------------------|
| Product Or Component Type | Head for non-illuminated push-button |
| Device Short Name | ZB5 |
| Bezel Material | Dark grey plastic |
| Head Type | Standard |
| Mounting Diameter | 0.87 in (22 mm) |
| Sale Per Indivisible Quantity | 1 |
| Shape Of Signaling Unit Head | Round |
| Type Of Operator | spring return |
| Operator Profile | Blue mushroom Ø 40 mm, unmarked |
| Device Presentation | Basic element |

Complementary

| Cad Overall Width | 1.57 in (40 mm) |
|-----------------------------|--|
| Cad Overall Height | 1.57 in (40 mm) |
| Cad Overall Depth | 2.05 in (52 mm) |
| Net Weight | 0.10 lb(US) (0.046 kg) |
| Mechanical Durability | 5000000 cycles |
| Station Name | XALD 1 cut-out XALK 1 cut-out |
| Electrical Composition Code | C1 9 single front mounting C2 9 single and double front mounting C11 3 single front mounting C15 1 single front mounting SF1 3 single front mounting SR1 3 single rear mounting |
| Compatibility Code | ZR5 |

ompatibility Code

ZB5

Environment

| Protective Treatment | тн |
|--|----------------------|
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -40158 °F (-4070 °C) |
| Overvoltage Category | Class II IEC 60536 |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Ip Degree Of Protection | IP66 IEC 60529 |
|---------------------------------------|---|
| | IP69 |
| | IP69K |
| Nema Degree Of Protection | NEMA 13 |
| | NEMA 4X |
| Resistance To High Pressure Washer | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m |
| Ik Degree Of Protection | IK03 conforming to IEC 50102 |
| Standards | UL 508 |
| | IEC 60947-1 |
| | JIS C8201-5-1 |
| | CSA C22.2 No 14 |
| | IEC 60947-5-4 |
| | IEC 60947-5-1 |
| | JIS C8201-1 |
| Product Certifications | BV |
| | CSA |
| | LROS (Lloyds register of shipping) |
| | GL |
| | UL Listed |
| | DNV |
| Vibration Resistance | 5 gn 2500 Hz)IEC 60068-2-6 |
| Shock Resistance | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 |
| | 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27 |

Ordering and shipping details

| Category | US10CS222467 |
|-------------------|---------------|
| Discount Schedule | 0CS2 |
| Gtin | 3389110904949 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.46 in (8.800 cm) |
| Package 1 Width | 1.73 in (4.400 cm) |
| Package 1 Length | 2.13 in (5.400 cm) |
| Package 1 Weight | 1.66 oz (47.000 g) |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 42 |
| Package 2 Height | 5.91 in (15.000 cm) |
| Package 2 Width | 11.81 in (30.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 5.09 lb(US) (2.309 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration | | | |
|---------------------------|---|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration | | | |
| China Rohs Regulation | China RoHS declaration | | | |
| Environmental Disclosure | Product Environmental Profile | | | |
| Circularity Profile | End of Life Information | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | |

Dimensions Drawings

Dimensions



| | Ø in mm | Ø in in. |
|--------|---------|----------|
| ZB5AC• | 40 | 1.57 |
| ZB5AR• | 60 | 2.36 |

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board




(1) Diameter on finished panel or support

(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. (3) \emptyset 22.5 mm recommended (\emptyset 22.3 $_0^{+0.4}$) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0^{+0.016}$)

| | | | | 0 . |
|---|---------|----------|---------|----------|
| Connections | a in mm | a in in. | b in mm | b in in. |
| By screw clamp terminals or plug-in connector | 40 | 1.57 | 30 | 1.18 |
| By Faston connectors | 45 | 1.77 | 32 | 1.26 |
| On printed circuit board | 30 | 1.18 | 30 | 1.18 |

Detail of Lug Recess




(1) Diameter on finished panel or support

- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) \emptyset 22.5 mm recommended (\emptyset 22.3 $_0^{+0.4}$) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0^{+0.016}$)

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer's Side)




A: 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. B: 40 mm min. Dimensions in in.



A: 1.18 in. min. **B:** 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- $_{\bullet}\,$ Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
 - $_{\circ}$ every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
 - with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board


Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ01•
- **3** 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ01•


Dimensions An + 18.1 relate to the Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 holes for centring adapter ZBZ01•.

Technical Description

Electrical Composition Corresponding to Code C1



Electrical Composition Corresponding to Code C2



Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Electrical Composition Corresponding to Code C15

1 N/O



1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



Legend

Single contact



Double contact



Light block



Possible location

