


Product data sheet

Specifications



COPPER CONNECTION 250A VERTICAL 4P/UNIVERSAL POWER SUPPLY W600

04062

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

Main

Range	Lineryg
Range Of Product	Lineryg
Product Or Component Type	Connection
Product Name	Lineryg BW
Product Name	Prisma Prisma P enclosure Prisma Prisma G enclosure Lineryg Lineryg BW busbar
Accessory / Separate Part Category	Current distribution accessory
Provided Equipment	Without cable
Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product Certifications	ASEFA

Complementary

Cubicle-Device Connection	Lineryg BW universal power supply block
Poles Description	4P
Installation Description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed Device	ComPact: fixed INS250 - control: direct front rotary handle vertical installation ComPact: fixed INV250 - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle vertical installation ComPact: fixed INV100 - control: direct front rotary handle vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: toggle vertical installation ComPact: fixed NSX250 without earth leakage protection - control: toggle vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle vertical installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle vertical installation ComPact: fixed INV250 - control: lateral handle vertical installation ComPact: fixed INS250 - control: lateral handle vertical installation ComPact: fixed INV200 - control: direct front rotary handle vertical installation ComPact: fixed INV160 - control: direct front rotary handle vertical installation

[Ie] Rated Operational Current 250 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[In] Rated Current	250 A
Net Weight	1.82 kg
Quantity Per Set	Set of 4

vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle vertical 3P 4 direct with long terminal shield 9
600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed toggle vertical 3P 4 direct with long terminal shield 9
600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed toggle vertical 4P 3 direct with long terminal shield 9
600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed toggle vertical 4P 3 direct with long terminal shield 9
600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9
600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9
600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9
600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9
600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed toggle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed toggle vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed toggle vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11
600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11
600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	16.5 cm
Package 1 Length	28.5 cm
Package 1 Weight	1.83 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile