Product data sheet

Specification





Head for key selector switch, Harmony XB5, flush mounted 8D1 3 pos stay put

ZB5FG3D

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 90.30 USD

Main

Range Of Product	Harmony XB5					
Product Or Component Type	Head for key selector switch					
Device Short Name	ZB5					
Bezel Material	Dark grey plastic					
Mounting Diameter	1.20 in (30.5 mm)					
Head Type	Built-in-flush					
Sale Per Indivisible Quantity	1					
Shape Of Signaling Unit Head	Round					
Type Of Operator	stay put					
Operator Profile	Black key switch					
Operator Position Information	3 positions +/- 45°					
Type Of Keylock	Key 3131A Dom 8D1					
Key Withdrawal Position	Center					

Complementary

Cad Overall Width	1.46 in (37 mm)					
Cad Overall Height	1.46 in (37 mm)					
Cad Overall Depth	2.83 in (72 mm)					
Net Weight	0.15 lb(US) (0.069 kg)					
Mechanical Durability	1000000 cycles					
Electrical Composition Code	C4 6 single and double front mounting C5 5 single front mounting C6 5 single and double front mounting C7 4 single front mounting C8 4 single and double front mounting C11 3 single front mounting C3 6 single front mounting SF1 3 single front mounting					

Environment

Protective Treatment	TH	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Overvoltage Category	Class II IEC 60536			
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K			
Nema Degree Of Protection	NEMA 13 NEMA 4X			
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m			
Ik Degree Of Protection	IK03 conforming to IEC 50102			
Standards	IEC 60947-5-4 JIS C8201-5-1 IEC 60947-1 CSA C22.2 No 14 IEC 60947-5-1 UL 508 JIS C8201-1			
Product Certifications	DNV CSA UL Listed LROS (Lloyds register of shipping) GL BV			
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6			
Shock Resistance 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27				

Ordering and shipping details

Category	US10CS222467	
Discount Schedule	0CS2	
Gtin	3606481340191	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE 1		
Number Of Units In Package 1			
Package 1 Height	3.39 in (8.6 cm)		
Package 1 Width	1.69 in (4.3 cm)		
Package 1 Length	2.05 in (5.2 cm)		
Package 1 Weight	2 22 pz (63 g)		



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	End of Life Information					
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

Dimensions Drawings

Dimensions




e: Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

ZB5FG3D

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors



(1) Diameter on finished panel or support


(2) Ø30.75 mm recommended (Ø30.5 $_0^{+0.5}$) / Ø1.21 in. recommended (Ø1.20 in. $_0^{+0.0196}$)


0				0
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	40	1.57
By Faston connectors	45	1.77	40	1.57


Technical Description














Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



1 N/O



1 N/C



1 N/O + N/C or 1 N/O + N/O or 1 N/C + N/C



Legend

Single contact



Double contact



Light block



Possible location



Sequence of Contacts Fitted to 2-position Selector Switch Body

Position 315°



Push	Position	Тор				
		Bottom				
	Location		Left	Centre	Right	
	State		0	0	0	
Contacts	N/O		open	open	open	
	N/C		closed	closed	closed	

Position 45°



		Тор			
Push	Position	Bottom			
	Location		Left	Centre	Right
	State		1	1	1
Contacts	N/O		closed	closed	closed
	N/C		open	open	open