

Product data sheet

Specifications



Miniature circuit breaker (MCB), Acti9 NG125N, 4P, 100A, C curve, 25kA (IEC/EN 60947-2)

18660

Main

Range Of Product	NG125
Range	Acti9
Product Name	Acti9 NG125
Product Or Component Type	Miniature circuit-breaker
Device Short Name	NG125N
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	100 A at 40 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	20 kA Icu at <= 500 V DC conforming to EN/IEC 60947-2 10 kA Icu at 500 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	380...415 V AC 50/60 Hz 500 V AC 50/60 Hz <= 500 V DC 220...240 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic Tripping Limit	8 x In
[Ics] Rated Service Breaking Capacity	37.5 kA 75 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 18.75 kA 75 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7.5 kA 75 % conforming to EN/IEC 60947-2 - 500 V AC 50/60 Hz 20 kA 100 % conforming to EN/IEC 60947-2 - <= 500 V DC
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Control Type	Manual tripping test Toggle
Local Signalling	ON/OFF indication Trip indicator
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	12
Height	103 mm
Depth	81 mm
Width	108 mm
Net Weight	0.96 kg
Mechanical Durability	20000 cycles
Electrical Durability	5000 cycles
Provision For Padlocking	Padlockable
Locking Options Description	Integrated padlocking
Connections - Terminals	Tunnel type terminals16...70 mm² rigid Tunnel type terminals10...50 mm² flexible
Wire Stripping Length	20 mm
Tightening Torque	6 N.m
Earth-Leakage Protection	Separate block

Environment

Standards	EN/IEC 60947-2
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ik Degree Of Protection	IK05 conforming to EN/IEC 62262
Pollution Degree	3 conforming to IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.600 cm
Package 1 Width	12.400 cm
Package 1 Length	15.500 cm
Package 1 Weight	1.041 kg
Unit Type Of Package 2	S03

Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	13.084 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information