Product datasheet





complete manual source changeover assembly, FXM160, Compact INS250-160 switch disconnectors, 160 A, 3 poles

31144

Main

Range Of Product	INS250
Range	TransferPacT ComPact
Device Short Name	INS250
Product Or Component Type	Manual transfer switch
Device Application	Change source of supply
Range Compatibility	ComPact ComPacT INS INS250 switch disconnector
Poles Description	3P
Network Type	AC DC
Network Frequency	50/60 Hz
Mounting Mode	Fixed
Upside Connection	Front
Downside Connection	Front
Suitability For Isolation	Yes
Contact Position Indicator	Yes
[Icm] Rated Short-Circuit Making Capacity	30 kA switch-disconnector alone 690 V AC at 50/60 Hz 330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz

Complementary

Transfer Switch Class	PC
Number Of Contact Position	3
Control Type	Direct front rotary handle
Operating Mode	Manual
Mounting Support	Plate Rail
Locking Options Description	Padlocking in OFF position
[le] Rated Operational Current	AC-22A: 160 A AC 50/60 Hz 220/240 V AC-22A: 160 A AC 50/60 Hz 380/415 V AC-22A: 160 A AC 50/60 Hz 440/480 V AC-22A: 160 A AC 50/60 Hz 500/525 V AC-22A: 160 A AC 50/60 Hz 660/690 V AC-23A: 160 A AC 50/60 Hz 220/240 V AC-23A: 160 A AC 50/60 Hz 380/415 V AC-23A: 160 A AC 50/60 Hz 380/415 V AC-23A: 160 A AC 50/60 Hz 500/525 V AC-23A: 160 A AC 50/60 Hz 440/480 V AC-23A: 160 A AC 50/60 Hz 500/525 V AC-23A: 160 A AC 50/60 Hz 660/690 V DC-22A: 160 A DC 125 V 2 poles in series DC-23A: 160 A DC 125 V 2 poles in series

Life Is On Schneider Apr 26, 2024

[Ith] Conventional Free Air Thermal Current	160 A at 60 °C
Rated Duty	Uninterrupted
Intermittent Duty Class	Class 120 - 60 %
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-3 125 V DC conforming to IEC 60947-3
Mechanical Interlocking	With mechanical interlocking
Mechanical Durability	15000 cycles
Electrical Durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-22A: 1500 cycles 125 V DC 2 poles in series DC-23A: 1500 cycles 125 V DC 2 poles in series
Connection Pitch	35 mm
[Icw] Rated Short-Time Withstand Current	1.8 kA during 30 s conforming to IEC 60947-3 2.2 kA during 20 s conforming to IEC 60947-3 4.9 kA during 3 s conforming to IEC 60947-3 8.5 kA during 1 s conforming to IEC 60947-3
Height	136 mm
Width	295 mm
Depth	131 mm
Net Weight	6.4 kg

Environment

Standards	IEC 60947-3 IEC 60947-1
Product Certifications	СВ
Electrical Shock Protection Class	Class II
Ip Degree Of Protection	IP40 conforming to IEC 60947-3
Pollution Degree	3
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.500 cm
Package 1 Width	16.500 cm
Package 1 Length	40.000 cm
Package 1 Weight	6.400 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration