

Product data sheet

Specifications



switch disconnecter, Compact
INS80, 80A, standard version with
black rotary handle, 4 poles

28905

Main

Range	ComPact
Product Name	ComPacT INS
Product Or Component Type	Switch disconnecter
Poles Description	4P
Network Type	AC DC
Network Frequency	50/60 Hz
[Ie] Rated Operational Current	AC-23A: 40 A AC 50/60 Hz 500 V AC-23A: 63 A AC 50/60 Hz 440/480 V 2 poles in series AC-22A: 80 A AC 50/60 Hz 220/240 V 4 poles in series AC-22A: 80 A AC 50/60 Hz 380/415 V 4 poles in series AC-22A: 80 A AC 50/60 Hz 440/480 V AC-22A: 80 A AC 50/60 Hz 500 V AC-23A: 72 A AC 50/60 Hz 380/415 V AC-23A: 80 A AC 50/60 Hz 220/240 V DC-22A: 80 A DC 50/60 Hz 125 V 2 poles in series DC-23A: 80 A DC 50/60 Hz 125 V 2 poles in series DC-22A: 80 A DC 50/60 Hz 250 V 4 poles in series DC-23A: 80 A DC 250 V 4 poles in series
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	80 A at 60 °C
[Icm] Rated Short-Circuit Making Capacity	15 kA switch-disconnector alone 500 V AC at 50/60 Hz 75 kA with upstream protection circuit breaker 500 V AC at 50/60 Hz
[Ue] Rated Operational Voltage	500 V AC 50/60 Hz 250 V DC
Suitability For Isolation	Yes
Contact Position Indicator	Yes
Visible Break	No
Pollution Degree	3

Complementary

Control Type	Rotary handle
Handle Colour	Black
Mounting Mode	Fixed
Mounting Support	Plate DIN rail
Upside Connection	Front

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downside Connection	Front
Cable Cross Section	1.5...50 mm²
Maximum Power	AC-23: 22 kW at 500/525 V AC 50/60 Hz AC-23: 22 kW at 220/240 V AC 50/60 Hz AC-23: 37 kW at 380/415 V AC 50/60 Hz AC-23: 37 kW at 440 V AC 50/60 Hz
Rated Duty	Uninterrupted
Intermittent Duty Class	Class 120 - 60 %
Enclosure Dimensions For lthe	190 mm x 115 mm x 55 mm
[Icw] Rated Short-Time Withstand Current	0.067 kA during 20 s conforming to IEC 60947-3 1.73 kA during 3 s conforming to IEC 60947-3 3 kA during 1 s conforming to IEC 60947-3 5.5 kA during 30 s conforming to IEC 60947-3
Mechanical Durability	20000 cycles
Electrical Durability	AC-22A: 1500 cycles 220/240 V AC 50/60 Hz AC-22A: 1500 cycles 380/415 V AC 50/60 Hz 4 poles in series AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 220/240 V AC 50/60 Hz AC-23A: 1500 cycles 380/415 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz DC-22A: 1500 cycles 250 V DC 50/60 Hz 4 poles in series DC-23A: 1500 cycles 250 V DC 4 poles in series
Connection Pitch	18 mm
Height	85 mm
Width	90 mm
Depth	62.5 mm
Net Weight	0.6 kg

Environment

Standards	IEC 60947-3 IEC 60947-1
Product Certifications	CCC KEMA-KEUR
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.700 cm
Package 1 Width	10.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	650.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18

Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	12.070 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	50.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	109.784 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov