


Product data sheet

Specifications



circuit breaker Compact NS100H - TMD - 50 A - 1 pole 1d

29596

ⓘ Discontinued

Main

Range Of Product	Compact NS100...630
Product Or Component Type	Circuit breaker
Device Short Name	Compact NS100H
Circuit Breaker Name	Compact NS100H
Device Application	Distribution
Poles Description	1P
Protected Poles Description	1t
Network Type	DC AC
Network Frequency	50/60 Hz
[In] Rated Current	100 A at 40 °C 100 A at 65 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	250 V DC conforming to IEC 60947-2 277 V AC 50/60 Hz conforming to IEC 60947-2
Breaking Capacity Code	H
Breaking Capacity	40 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 40 kA at 277 V AC 50/60 Hz conforming to NEMA AB1 HIC 40 kA Icu at 220 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 277 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 250 V DC 1P conforming to IEC 60947-2 85 kA Icu at 48/125 V DC 1P conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	40 kA at 220 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 277 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 250 V DC conforming to IEC 60947-2 85 kA at 48/125 V DC conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	50 A at 40 °C
Protection Type	Short-circuit protection (magnetic) Overload protection (thermal)
Pollution Degree	3 conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Control Type	Toggle
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles 277 V AC 50/60 Hz In conforming to IEC 60947-2 20000 cycles 277 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Connection Pitch	35 mm
Local Signalling	Positive contact indication
Magnetic Tripping Current	300 A 1000 A 500 A 1250 A 190 A 800 A 640 A 260 A
Long Time Pick-Up Adjustment Type Ir	Fixed
Long Time Pick-Up Adjustment Range	0.8...1 x In
Instantaneous Pick-Up Adjustment Type Ii	Fixed
Instantaneous Pick-Up Adjustment Range	500 A
Height	161 mm
Width	35 mm
Depth	86 mm

Environment

Standards	IEC 60947-2
Product Certifications	ASEFA ASTA LCIE KEMA
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Contractual warranty

Warranty	18 months
----------	-----------