Product datasheet

Specifications





base unit SEP080 for Sepam series 80 - 24...250 V - with basic UMI

59703

Main

| Range Of Product | Sepam series 80 |
|-----------------------------|-----------------|
| Device Short Name | SEP080 |
| User Machine Interface Type | Without |

Complementary

| complementary | |
|---------------------------|--|
| Output Type | Annunciation relay: 100240 V AC 47.563 Hz continuous current: 2 A breaking capacity: 1 A cos φ > 0.3 Annunciation relay: 127 V DC continuous current: 2 A breaking capacity: 0.5 A L/R < 20 ms Annunciation relay: 220 V DC continuous current: 2 A breaking capacity: 0.15 A L/R < 20 ms Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 2 A L/R < 20 ms Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 2 A L/R < 20 ms Control relay: 48 V DC continuous current: 2 A breaking capacity: 1 A L/R < 20 ms Control relay: 100240 V AC 47.563 Hz continuous current: 8 A breaking capacity: 5 A cos φ > 0.3 making capacity: < 15 A for 200 ms |
| | Control relay: 100240 V AC 47.563 Hz continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 40 ms |
| | making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.5 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.7 A resistive |
| | Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.7 A resistive making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.1 A L/R < 40 ms making capacity: < 15 A for 200 ms |
| | Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 20 ms making capacity: < 15 A for 200 ms |
| | Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.3 A resistive making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 4 A L/R < 40 ms |
| | making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 6 A L/R < 20 ms making capacity: < 15 A for 200 ms |
| | Control relay: 24 V DC continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 1 A L/R < 40 ms |
| | making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 2 A L/R < 20 ms |
| | making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 4 A resistive making capacity: < 15 A for 200 ms |
| [Us] Rated Supply Voltage | 24/250 V DC tolerance: - 2010 % maximum consumption: < 16 W |
| Supply Inrush Current | < 10 A for 10 ms at 24/250 V DC |
| Battery Type | Lithium 3.6 V size: 1/2 AA |
| Battery Life | 10 year(s) (Sepam energized) 8 year(s) (Sepam not energized) |
| Mounting Mode | Fixed |
| Mounting Support | Plate |
| | |

| Height | 222 mm |
|---|---|
| Width | 264 mm |
| Depth | 89.7 mm |
| Net Weight | 2.4 kg |
| Power Frequency Dielectric Withstand | 2 kV during 1 min conforming to IEC 60255-5 1 kV (indication output) during 1 min conforming to ANSI C37.90 1.5 kV (control output) during 1 min conforming to ANSI C37.90 |
| [Uimp] Rated Impulse Withstand Voltage | 5 kV (1.2/50 µs) conforming to IEC 60255-5 |
| Mechanical Robustness | Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3 Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3 |
| | Jolts de-energized (level: 2) : 20 Gn/16 ms conforming to IEC 60255-21-2 Shocks de-energized (level: 2) : 27 Gn/11 ms conforming to IEC 60255-21-2 Shocks in operation (level: 2) : 10 Gn/11 ms conforming to IEC 60255-21-2 Vibrations de-energized (level: 2) : 2 Gn, 10 Hz150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: 2) : 1 Gn, 10 Hz150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: 2) : 2 Hz13.2 Hz, a = +/- 1 mm conforming to IEC 60068-2-6 |

Environment

| Standards | CSA C22.2 No 0.17-00 EN 50263 CSA C22.2 No 94-M91 CSA C22.2 No 14-95 UL 508 |
|---------------------------|---|
| Product Certifications | CE UL 508 file N° 212533 C22.2 file N° 210625 |
| Fire Resistance | 650 °C conforming to IEC 60695-2-11 |
| Ip Degree Of Protection | Other panels: IP20 conforming to IEC 60529 Front panel: IP52 conforming to IEC 60529 |
| Nema Degree Of Protection | Type 12 conforming to NEMA |
| Immunity To Microbreaks | 100 ms |

Life Is On Scheider

| Electromagnetic Compatibility | Fast transient bursts: (immunity tests-conducted disturbances), A and B, 4kV, 2.5 |
|-------------------------------|--|
| o , , , | kHz/2 kV, 5 kHz, conforming to IEC 60255-22-4 |
| | Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, |
| | conforming to IEC 61000-4-4 |
| | Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), |
| | III, 10 V, conforming to IEC 60255-22-6 |
| | Immunity to magnetic fields at network frequency: (immunity tests-radiated |
| | disturbances), IV, 30 A/m (continuous)-300 A/m (13 s), conforming to IEC 61000-4-8 |
| | Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 |
| | MHz2 GHz, conforming to IEC 61000-4-3 |
| | Surges: (immunity tests-conducted disturbances), III, 2 kV CM, 1 kV MD, conforming to IEC 61000-4-5 |
| | Conducted disturbance emission: (emission tests), conforming to IEC 60255-25 |
| | Disturbing field emission: (emission tests), conforming to IEC 60255-25 |
| | Disturbing field emission: (emission tests), A, conforming to EN 55022 |
| | Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV |
| | contact, conforming to ANSI C37.90.3 |
| | Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2 |
| | Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1 |
| | Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz 1 GHz, conforming to IEC 60255-22-3 |
| | 1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV MD, conforming to IEC 60255-22-1 |
| | 1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 2.5 kV MD, conforming to ANSI C37.90.1 |
| | 100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV MD, conforming to IEC 61000-4-12 |
| | Conducted disturbance emission: (emission tests), A, conforming to EN 55022 |
| | Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz 1 GHz, conforming to ANSI C37.90.2 |
| | Voltage interruptions: (immunity tests-conducted disturbances), 100 % during 100 |
| | ms, conforming to IEC 60255-11 |
| Climatic Withstand | Continuous exposure to damp heat (in operation) : Cab: 10 days, 93 % RH, 40 °C conforming to IEC 60068-2-78 |
| | Continuous exposure to damp heat (in storage) : Cab: 56 days, 93 % RH, 40 °C conforming to IEC 60068-2-78 |
| | Continuous exposure to damp heat (in storage) : Db: 6 days, 95 % RH, 55 °C conforming to IEC 60068-2-30 |
| | Exposure to cold (in operation) : Ad: - 25 °C conforming to IEC 60068-2-1 |
| | Exposure to cold (in storage) : Ab: - 25 °C conforming to IEC 60068-2-1 |
| | Exposure to dry heat (in operation) : Bd: 70 °C conforming to IEC 60068-2-2 |
| | Exposure to dry heat (in storage) : Bb: 70 °C conforming to IEC 60068-2-2 |
| | Salt mist (in operation) : Kb/2: 6 days conforming to IEC 60068-2-52 |
| | Temperature variation with specified variation rate (in storage) : Nb: - 25 °C to 70 °C, 5 °C/min conforming to IEC 60068-2-14 |
| | Influence of corrosion/gaz test 2 (in operation) : 21 days, 75 % RH, 25 °C, 0.5 ppm |
| | H2S, 1 ppm S02 conforming to IEC 60068-2-60 |
| | |
| | Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm |

Packing Units

| V | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 28.5 cm |
| Package 1 Width | 19.0 cm |
| Package 1 Length | 36.0 cm |
| Package 1 Weight | 3.1 kg |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 40.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 9.34 kg |

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |