# **Product datasheet**

Specifications





# iCT 63A 2NO 24V 50Hz contactor

A9C20162

#### Main

Range Of Product	Acti9
Product Name	Acti9 iCT
Product Or Component Type	Contactor
Device Short Name	iCT
Device Application	Motor-heating-lighting
Poles	2P
[le] Rated Operational Current	63 A AC-7A 20 A AC-7B
Pole Contact Composition	2 NO
Network Type	AC
Control Type	Remote control
[Uc] Control Circuit Voltage	24 V AC 50 Hz

### Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	250 V AC 50 Hz
Maximum Power	1.6 W at 250 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 KV
Control Signal Type	Maintained
Switching Frequency	100 switching operations/day
Local Signalling	Action indicator
Hold-In Power Consumption In Va	4.6 VA
Inrush Power In Va	34 VA
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	85 mm
Width	36 mm
Depth	68.5 mm
Colour	White

Mechanical Durability	1000000 cycles
Electrical Durability	100000 cycles IEC/EN 61095 63 A 50 Hz AC-7A 30000 cycles IEC/EN 61095 20 A 50 Hz AC-7B 30000 cycles IEC/EN 61095 50 Hz AC-7C 100000 cycles EN/IEC 60947-4-1 50 Hz AC-1 30000 cycles EN/IEC 60947-4-1 50 Hz AC-3 30000 cycles EN/IEC 60947-4-1 50 Hz AC-5a 30000 cycles EN/IEC 60947-4-1 50 Hz AC-5b
Connections - Terminals	Control circuit: tunnel type terminals2 cable(s) 1.5 mm <sup>2</sup> rigid Control circuit: tunnel type terminals1 cable(s) 1.52.5 mm <sup>2</sup> rigid Power circuit: tunnel type terminals1 cable(s) 616 mm <sup>2</sup> flexible Power circuit: tunnel type terminals1 cable(s) 625 mm <sup>2</sup> rigid Control circuit: tunnel type terminals2 cable(s) 1.52.5 mm <sup>2</sup> flexible
Tightening Torque	Control circuit: 0.8 N.m Power circuit: 3.5 N.m
Product Compatibility	IACTc IACTs IATEt IACTp
Compatibility Code	ICT
Market Segment	Residential Small commercial

### Environment

IEC/EN 61095
30 dB
1.6 W at 50/60 Hz
IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
2
2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
95 % at 55 °C
2000 m
-560 °C
-4070 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	11.400 cm
Package 1 Length	12.200 cm
Package 1 Weight	258.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	11.500 cm
Package 2 Width	12.500 cm
Package 2 Length	25.000 cm

Package 2 Weight	1.620 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	10.188 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations