Product datasheet

Specifications





Easy UPS 3M 100kVA 400V 3:3 UPS for external batteries, Startup 5x8

E3MUPS100KHS

Overview

design making your business continuity easy. Ideal for small and medium data centers and other business critical applications, this UPS is EcoStruxure-ready to give you peace of mind with cloud-based remote monitoring and management. It is supplied without batteries, so you can easily customize your battery solution. Includes 5x8 start-up service.
Usually Ships within 6 Weeks

Main

Main Input Voltage	400 V 3 phases	
Other Input Voltage	380 V	
	415 V	
Main Output Voltage	400 V 3 phases	
Other Output Voltage	380 V	
	415 V	
Rated Power In W	100 kW	
Rated Power In Va	100 kVA	
Provided Equipment	Dust filter	
	Installation guide	
	Start-up service	

Batteries & Runtime

Efficiency	View Efficiency Graph 🖾
Battery Type	External battery system
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

Physical

Colour	White (RAL 9003)
Height	91.5 cm
Width	36 cm
Depth	85 cm
Net Weight	145 kg
Usb Compatible	Yes

Input

Maximum Input Current	177 A
Max Short Time Withstand Current	10 kA
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.99
Input Voltage Limits	342477 V
Number Of Input Connectors	1 hard wire 5-wire (3P + N + E)
Network Frequency	4070 Hz

Output

Maximum Configurable Power In Va	100 kVA
Maximum Configurable Power In W	100 kW
Output Frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic Distortion	Less than 3 %
Output Harmonic Distortion	< 3% linear load and < 5% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Ups Туре	Double conversion online
Wave Type	Sine wave
Bypass Type	Built-in static bypass
Crest Factor	3:1

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	04921 ft
Ambient Air Temperature For Storage	-2555 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	65 dBA
Heat Dissipation	18767 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Control Panel	Touch screen LCD user interface

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	112.000 cm
Package 1 Width	48.000 cm

 Package 1 Length
 96.000 cm

 Package 1 Weight
 165.000 kg

Contractual warranty

Warranty

1 year on-site repair or replace with factory authorized Start-Up

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information