Product datasheet

Main





Contactor, Easy TeSys Control, LC1E, 4P(4NO),AC-1,<=440V,16A,24V AC coil

LC1E06004B7



! Discontinued on: May 19, 2023



Range	Easy TeSys	
Range Of Product	Easy TeSys Control	
Product Or Component Type	Contactor	
Device Short Name	LC1E	
Contactor Application	Resistive load	
Utilisation Category	AC-1	
Poles Description	4P	

16 A (at <60 °C) at <= 415 V AC AC-1 for power circuit

Power circuit: <= 690 V AC 50/60 Hz

24 V AC 50/60 Hz

Complementary

[Uc] Control Circuit Voltage

[Ue] Rated Operational Voltage

[le] Rated Operational Current

Pole Contact Composition	4 NO
[Ith] Conventional Free Air Thermal Current	16 A (at 60 °C) for power circuit
Irms Rated Making Capacity	60 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated Breaking Capacity	48 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	80 A 40 °C - 10 s for power circuit 45 A 40 °C - 60 s for power circuit 20 A 40 °C - 600 s for power circuit
Associated Fuse Rating	10 A gG at <= 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 12 A gG at <= 690 V coordination type 1 for power circuit
Average Impedance	2.5 mOhm - Ith 16 A 50 Hz for power circuit
Power Dissipation Per Pole	0.09 W AC-3 1 W AC-1
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Mechanical Durability	10000000 cycles
Electrical Durability	1400000 cycles AC-3 150000 cycles AC-1

Life Is On Schneider Apr 23, 2024

Oombrol Circuit Torre	40.450/0044
Control Circuit Type	AC at 50/60 Hz
Control Circuit Voltage Limits	0.851.1 Uc (55 °C):operational 50/60 Hz 0.30.6 Uc (55 °C):drop-out 50/60 Hz
Inrush Power In Va	95 VA 50 Hz cos phi 0.75 (at 20 °C) 95 VA 60 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	8.3 VA 50 Hz cos phi 0.3 (at 20 °C) 8.5 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W for control circuit
Operating Time	1222 ms on closing 419 ms on opening
Maximum Operating Rate	1800 cyc/h 60 °C
Connections - Terminals	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end
Tightening Torque	Power circuit: 1.2 N.m Control circuit: 1.2 N.m
Minimum Switching Voltage	17 V for control circuit
Minimum Switching Current	5 mA for control circuit
Insulation Resistance	> 10 MOhm for control circuit
Non-Overlap Time	1.5 ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting Support	Plate DIN rail
Environment	
Standards	IEC 60947-1

Standards	IEC 60947-1
Product Certifications	CE EAC
Ip Degree Of Protection	IP2X conforming to IEC 60529
Protective Treatment	TH (pollution degree 3) conforming to IEC 60068-2-30
Permissible Ambient Air Temperature Around The Device	-2070 °C at Uc -6080 °C storage -555 °C operation
Operating Altitude	3000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Vibrations contactor open (1.5 Gn, 5300 Hz) Vibrations contactor closed (3 Gn, 5300 Hz) Shocks contactor open (7 Gn for 11 ms) Shocks contactor closed (10 Gn for 11 ms)
Height	74 mm

Width	45 mm
Depth	80 mm
Net Weight	0.34 ka

Packing Units

Unit Type Of Package 1	PCE



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins