# **Product datasheet**

Specifications





Motor Management, TeSys T, motor controller, CANopen, 6 logic inputs, 3 relay logic outputs, 0.4 to 8A, 24 VDC

LTMR08CBD

① To be discontinued

Uiscontinued on: Dec 1, 2023

### Main

Range	TeSys
Product Name	TeSys T
Device Short Name	LTMR
Product Or Component Type	Motor controller
Device Application	Equipment monitoring and control
Measurement Current	0.48 A
[Us] Rated Supply Voltage	24 V DC
Current Consumption	56127 mA
Supply Voltage Limits	20.426.24 V DC
Communication Port Protocol	CANopen
Bus Type	CANopen ISO 1198 interface, addressing 1127, transmission rate 101000 kbit/s, SUB-D 9 with 4 twisted shielded pairs cable CANopen ISO 1198 interface, addressing 1127, transmission rate 101000 kbit/s, terminal block with 4 twisted shielded pairs cable

### Complementary

[Ui] Rated Insulation Voltage	690 V conforming to EN/IEC 60947-1 690 V conforming to CSA C22.2 No 14 690 V conforming to UL 508
[Uimp] Rated Impulse Withstand Voltage	6 kV current or voltage measurement circuit conforming to EN/IEC 60947-4-1 0.8 kV communication circuit conforming to EN/IEC 60947-4-1 0.8 kV supply, inputs and outputs conforming to EN/IEC 60947-4-1
Short-Circuit Withstand	100 kA conforming to EN/IEC 60947-4-1
Associated Fuse Rating	4 A gG for output 0.5 A gG for control circuit
Protection Type	Overload (long time) Phase failure Load fluctuation Phase imbalance Reverse polarity protection Thermal protection Earth-leakage protection Power factor variation Overload Locked rotor

Network And Machine Diagnosis Type	Trip context information Remaining operating time before overload tripping
	Starting current and time
	Event recording Motor control command recording
	Running hours counter/operating time
	Waiting time after overload tripping
	Trip history information
	Phase fault and earth fault trip counters
	Fault recording
Logic Input Number	6
Input Current	7 mA
Current State 0 Guaranteed	Logic input: < 5 V and <= 15 mA for 5 ms
Current State 1 Guaranteed	Logic input: < 15 V and 215 mA for 15 ms
Maximum Output Switching Frequency	2 Hz
Load Current	5 A at 250 V AC for logic output
	5 A at 30 V DC for logic output
Permissible Power	480 VA (AC-15), le = 2 A, 500000 cycles (output)
	30 W (DC-13), le = 1.25 A, 500000 cycles (output)
Maximum Operating Rate	1800 cyc/h
Contacts Type And Composition	1 NO + 1 NC fault signal 3 NO
Metering Type	Average current lavg
	Phase current I1, I2, I3 RMS
	Temperature Earth-fault current
	Imbalance current
Measurement Accuracy	515 % earth fault current internal measurement
	1 % voltage (100830 V)
	3 % power factor
	5 % earth fault current external measurement
	+/- 30 min/year internal clock 0,02 temperature
	1 % current
	5 % active and reactive power
Overvoltage Category	III
Connection Pitch	5.08 mm
Connections - Terminals	Control circuit: connector 1 cable(s) 0.252.5 mm <sup>2</sup> (AWG 24AWG 14) flexible with cable end
	Control circuit: connector 1 cable(s) 0.22.5 mm <sup>2</sup> (AWG 24AWG 14) flexible
	without cable end
	Control circuit: connector 1 cable(s) 0.252.5 mm <sup>2</sup> (AWG 24AWG 14) flexible without cable end
	Control circuit: connector 1 cable(s) 0.22.5 mm <sup>2</sup> (AWG 24AWG 14) solid without
	cable end
	Control circuit: connector 2 cable(s) 0.21 mm <sup>2</sup> (AWG 24AWG 14) flexible with cable and
	cable end Control circuit: connector 2 cable(s) 0.21.5 mm <sup>2</sup> (AWG 24AWG 14) flexible without cable end
	Control circuit: connector 2 cable(s) 0.51.5 mm² (AWG 24AWG 14) flexible
	without cable end
	Control circuit: connector 2 cable(s) 0.21 mm <sup>2</sup> (AWG 24AWG 14) solid without cable end
Tightening Torque	Control circuit: 0.50.6 N.m flat screwdriver 3 mm

Pollution Degree

3

Electromagnetic Compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Radiated RF fields, 3, 10 V/m, conforming to EN/IEC 61000-4-3 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Voltage dips and interruptions immunity test, 70 %, 500 ms, conforming to EN/IEC 61000-4-11 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Temperature sensor: surges (serial mode), 0.5 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5 Relay outputs and supply: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5
Width	91 mm
Height	61 mm
Depth	122.5 mm
Net Weight	0.53 kg
Web Services	Web server
Compatibility Code	LTMR

### Environment

Standards	EN 60947-4-1
	CSA C22.2 No 14
	IEC 60947-4-1
	UL 508
	IACS E10
Product Certifications	ATEX
	C-Tick
	EAC
	LROS (Lloyds register of shipping)
	NOM
	BV
	RINA
	KERI
	ABS
	UL
	CSA
	DNV
	RMRoS
	GL
	CCC
Protective Treatment	12 x 24 hour cycles conforming to EN/IEC 60068-2-30
	48 h conforming to EN/IEC 60070-2-11
	TH conforming to EN/IEC 60068
Fire Resistance	650 °C conforming to EN/IEC 60695-2-12
	960 °C conforming to UL 94
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4080 °C
Operating Altitude	<= 2000 m without derating
Mechanical Robustness	Vibrations mounted on symmetrical rail: 1 Gn, 5300 Hz conforming to EN/IEC 60068-2-6
	Vibrations plate mounted: 4 Gn, 5300 Hz conforming to EN/IEC 60068-2-6
	Shocks half sine wave acceleration: 15 Gn for 11 ms conforming to EN/IEC
	60068-2-27
Ip Degree Of Protection	
ip begree of Fiolection	IP20

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	10.0 cm
Package 1 Length	13.5 cm
Package 1 Weight	510.0 g
Unit Type Of Package 2	\$02
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.452 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information