


Product data sheet

Specifications



circuit breaker Compact NS400L - 150 A - 3 poles - fixed - without trip unit

32384

ⓘ Discontinued

Main

Range Of Product	NS400...630
Product Or Component Type	Basic frame
Device Short Name	Compact NS400L
Circuit Breaker Name	Compact NS400L
Poles Description	3P
Network Type	DC AC
Network Frequency	50/60 Hz
Control Type	Toggle
[In] Rated Current	320 A at 65 °C 400 A at 40 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2 750 V DC conforming to IEC 60947-2
Breaking Capacity Code	L
Breaking Capacity	130 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 200 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 50 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 HIC 100 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 130 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 75 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	130 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 75 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Pollution Degree	3 conforming to IEC 60947

Complementary

Mounting Mode	Fixed
Mounting Support	Backplate

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Upside Connection	Front
Downside Connection	Front
Circuit Breaker Ct Rating	150 A
Protection Type	Without protection
Mechanical Durability	15000 cycles conforming to IEC 60947-2
Electrical Durability	12000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 6000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2
Connection Pitch	45 mm
Height	255 mm
Width	140 mm
Depth	110 mm

Environment

Standards	IEC 60947-2
Product Certifications	ASEFA LCIE KEMA ASTA
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Contractual warranty

Warranty	18 months
----------	-----------