

Product data sheet

Specifications



circuit breaker Compact NS400L - STR53UE - 150 A - 4 poles 4d

32730

! Discontinued

Main

Range Of Product	Compact NS100...630
Product Or Component Type	Circuit breaker
Device Short Name	Compact NS400L
Circuit Breaker Name	Compact NS400L
Device Application	Distribution
Poles Description	4P
Protected Poles Description	3t 4t 3t + N/2
Neutral Position	Left
Network Type	DC AC
Network Frequency	50/60 Hz
[In] Rated Current	400 A at 40 °C 320 A at 65 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2 750 V DC conforming to IEC 60947-2
Breaking Capacity Code	L
Breaking Capacity	130 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 200 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 100 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 130 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	130 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Trip Unit Name	STR53UE F
Trip Unit Technology	Electronic
Trip Unit Rating	150 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protection Type	Instantaneous short-circuit protection Short time short-circuit protection Overload protection (long time) Protection of the fourth pole
Pollution Degree	3 conforming to IEC 60947

Complementary

Control Type	Toggle
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Circuit Breaker Ct Rating	150 A
Mechanical Durability	15000 cycles
Electrical Durability	12000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 6000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2
Connection Pitch	45 mm
Local Signalling	Positive contact indication
Neutral Protection Setting	No protection 1 x Ir 0.5 x Ir
Long Time Pick-Up Adjustment Type Ir	Adjustable 48 settings
Long Time Pick-Up Adjustment Range	0.4...1 x In
Long Time Delay Adjustment Type	Adjustable
[Tr] Long-Time Delay Adjustment Range	12...16 s 6 x Ir 138...200 s 1.5 x Ir 277...400 s 1.5 x Ir 3...4 s 6 x Ir 34...50 s 1.5 x Ir 6...8 s 6 x Ir 69...100 s 1.5 x Ir 8...15 s 1.5 x Ir 0.2...0.74 s 7.2 x Ir 0.4...0.5 s 6 x Ir 1...1.4 s 7.2 x Ir 1.5...2 s 6 x Ir 2...2.8 s 7.2 x Ir 4...5.5 s 7.2 x Ir 8.2...11 s 7.2 x Ir
Short-Time Pick-Up Adjustment Type Isd	Adjustable 8 settings
[Isd] Short-Time Pick-Up Adjustment Range	1.5...10 x Ir
Short-Time Delay Adjustment Type	Adj 4 setgs + const I ² t option
[Tsd] Short-Time Delay Adjustment Range	0.14...0.23 s 0.06...0.14 s 0.015...0.06 s 0.23...0.35 s
Instantaneous Pick-Up Adjustment Type Ii	Adjustable
Instantaneous Pick-Up Adjustment Range	1.5...11 x In
Display Type	LED
Height	255 mm
Width	185 mm

Depth	110 mm
-------	--------

Environment

Standards	IEC 60947-2
Product Certifications	KEMA ASTA ASEFA LCIE
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Contractual warranty

Warranty	18 months
----------	-----------