Specifications





3-phase control relay, Harmony Control Relays, 5A, 2CO, 380...480V AC

RM22TA33

Main

Range Of Product	Harmony Control Relays
Relay Type	Control relay
Product Or Component Type	3-phase control relay
Network Number Of Phases	3 phases
Relay Name	RM22TA
Relay Monitored Parameters	Phase sequence Phase failure detection Asymmetry
Time Delay Type	Adjustable 0.130 s, +/- 10 % of the full scale value Tt- time delay upon fault
Switching Capacity In Va	2000 VA
Measurement Range	380480 V voltage AC
Contacts Type And Composition	2 C/O

Complementary

· · · · · · · · · · · · · · · · · ·	
Reset Time	1500 ms at maximum voltage
Maximum Switching Voltage	250 V AC
Minimum Switching Current	10 mA at 5 V DC
Maximum Switching Current	8 A AC
[Us] Rated Supply Voltage	AC/DC
Supply Voltage Limits	304576 V AC
Operating Limits	- 20 % + 20 % Un
Power Consumption In Va	15 VA at 480 V AC 60 Hz
Voltage Detection Threshold	< 100 V AC
Supply Voltage Frequency	5060 Hz +/- 10 %
Output Contacts	2 C/O
Setting Accuracy Of The Switching Threshold	+/- 10 % of the full scale
Switching Threshold Drift	<= 0.05 % per degree centigrade depending permissible ambient air temperature <= 1 % within the supply voltage range
Setting Accuracy Of Time Delay	10 P
Time Delay Drift	<= 0.05 % per degree centigrade depending permissible ambient air temperature <= 1 % within the supply voltage range
Hysteresis	2 % fixed of selectable
Run-Up Delay At Power-Up	650 ms

Maximum Measuring Cycle	150 ms measurement cycle as true rms value
Voltage Range	380480 V phase to phase
Adjustment Of Asymmetry Threshold	515 % of Un selected
Repeat Accuracy	+/- 0.5 % for input and measurement circuit +/- 3 % for time delay
Measurement Error	< 1 % over the whole range with voltage variation < 0.05 %/°C with temperature variation
Response Time	<= 300 ms
Overvoltage Category	III conforming to IEC 60664-1 III conforming to UL 508
Insulation Resistance	> 100 MOhm at 500 V DC conforming to IEC 60255-27
Mounting Position	Any position
Connections - Terminals	Screw terminals, 2 x 0.52 x 2.5 mm ² (AWG 20AWG 14) solid without cable end Screw terminals, 2 x 0.22 x 1.5 mm ² (AWG 24AWG 16) flexible with cable end Screw terminals, 1 x 0.51 x 3.3 mm ² (AWG 20AWG 12) solid without cable end Screw terminals, 1 x 0.21 x 2.5 mm ² (AWG 24AWG 14) flexible with cable end
Tightening Torque	0.61 N.m conforming to IEC 60947-1
Housing Material	Self-extinguishing plastic
Status Led	LED (yellow) relay ON LED (green) power ON
Mounting Support	35 mm DIN rail conforming to IEC 60715
Electrical Durability	100000 cycles
Mechanical Durability	1000000 cycles
Utilisation Category	AC-15 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1 AC-1 conforming to IEC 60947-4-1 DC-1 conforming to IEC 60947-4-1
[Un] Rated Nominal Voltage	, self-powered
Safety Reliability Data	MTTFd = 388.1 years B10d = 350000
Contacts Material	Cadmium free
Control Type	With test button
Width	22.5 mm
Net Weight	0.09 kg

Environment

Immunity To Microbreaks

10 ms

Electromagnetic Compatibility	Immunity for regidential commercial and light industrial equipments conferming to		
Electromagnetic Compatibility	Immunity for residential, commercial and light-industrial environments conforming to IEC 61000-6-1		
	Immunity for industrial environments conforming to IEC 61000-6-2		
	Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3		
	Emission standard for industrial environments conforming to IEC 61000-6-4		
	Electrostatic discharge - test level: 6 kV level 3 (contact discharge) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV level 3 (air discharge) conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test - test level: 10 V/m level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test - test level: 4 kV level 4 (direct) conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test - test level: 2 kV level 4 (capacitive coupling) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV level 4 (common mode) conforming to IEC 61000-4-4		
		Surge immunity test - test level: 2 kV level 4 (differential mode) conforming to IEC 61000-4-5	
			Conducted and radiated emissions class B group 1 conforming to CISPR 11
			Conducted and radiated emissions class B conforming to CISPR 22
		Standards	IEC 60255-1
		Product Certifications	GL
		EAC	
	000		

	CE CSA UL RCM
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2050 °C at 60 Hz -2060 °C at 50 Hz AC/DC
Relative Humidity	9397 % at 2555 °C conforming to IEC 60068-2-30
Vibration Resistance	0.075 mm (f= 1058.1 Hz) not in operation conforming to IEC 60068-2-6 1 gn (f= 1058.1 Hz) not in operation conforming to IEC 60068-2-6 0.035 mm (f= 58.1150 Hz) in operation conforming to IEC 60068-2-6 0.5 gn (f= 58.1150 Hz) in operation conforming to IEC 60068-2-6
Shock Resistance	15 gn (duration = 11 ms) for not in operation conforming to IEC 60068-2-27 5 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27
Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529 IP40 (housing) conforming to IEC 60529 IP50 (front panel) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1 3 conforming to UL 508
Dielectric Test Voltage	2.5 kV, 1 min AC 50 Hz conforming to IEC 60255-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.6 cm
Package 1 Width	8.2 cm
Package 1 Length	9.5 cm
Package 1 Weight	104.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm

_

Package 2 Length	40.0 cm
Package 2 Weight	4.47 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	640
Package 3 Height	75.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	82.34 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free


Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings


Dimensions



Mounting and Clearance

Mounting and Clearance


Rail Mounting



Connections and Schema

3-Phase Control Relay

Wiring Diagram




L1,L2,L3 : Supply to be monitored 11-14,12 : 1st C/O contact of output relay 21-24,22 : 2nd C/O contact of output relay

Technical Description

Function Diagram

Phase Sequence Control, Phase Failure Detection (U measured < 0.7 x nominal supply voltage), and Asymmetry Detection



Legend

Tt Time delay after crossing of threshold
L1, L2, L3 Phases of the supply voltage monitored
A Asymmetry threshold
H Hysteresis
11-12, 11-14 Output relay connections
Relay status: black color = energized.