

# Product data sheet

Specifications



Circuit breaker frame, ComPact NS800N, 50kA/415VAC, 800A, fixed, manually operated, without trip unit, 3P

33230

 To be discontinued on: Apr 30, 2024

 To be discontinued

## Main

|  |  |
|--|--|
| Range  | ComPact  |
| Range Of Product                                     | ComPact NS630b...1600  |
| Device Short Name                                    | Compact NS800N   |
| Product Or Component Type                            | Basic frame  |
| Device Application                                   | Distribution   |
| Number Of Poles                                      | 3P   |
| [In] Rated Current                                   | 800 A at 50 °C   |
| [Ue] Rated Operational Voltage                       | 690 V AC 50/60 Hz  |
| Network Type   | AC   |
| Network Frequency                                    | 50/60 Hz   |
| Suitability For Isolation                            | Yes conforming to EN/IEC 60947-2   |
| Utilisation Category                                 | Category B   |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 30 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2<br>85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2<br>50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2<br>50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2<br>40 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level                                    | N 50 kA 415 V AC   |
| Control Type   | Toggle<br>Rotary handle  |
| Mounting Mode  | Fixed  |

## Complementary

|   |   |
|---|---|
| [UI] Rated Insulation Voltage                       | 800 V AC 50/60 Hz conforming to IEC 60947-2   |
| [Uimp] Rated Impulse Withstand Voltage              | 8 kV conforming to IEC 60947-2  |
| [Ics] Rated Service Short-Circuit Breaking Capacity | 30 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation)<br>40 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation)<br>50 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation)<br>50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation)<br>50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) |
| [Icw] Rated Short-Time Withstand Current            | 19.2 kA 1 s conforming to IEC 60947-2   |
| Integral Instant Protection                         | 40 kA   |
| Mechanical Durability                               | 10000 cycles conforming to IEC 60947-2  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                       |  |
|-----------------------|--|
| Electrical Durability | 2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2<br>4000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2<br>5000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2<br>6000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 |
| Power Losses          | 15 W   |
| Mounting Support      | Backplate  |
| Connection Pitch      | 70 mm  |
| Protection Type       | Without protection   |
| Height (H)            | 327 mm   |
| Width (W)             | 210 mm   |
| Depth (D)             | 147 mm   |

## Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| Standards                             | IEC 60947-2                  |
| Product Certifications                | ASEFA<br>ASTA<br>LCIE        |
| Pollution Degree                      | 3 conforming to IEC 60947    |
| Ip Degree Of Protection               | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection               | IK07 conforming to EN 50102  |
| Ambient Air Temperature For Operation | -25...70 °C                  |
| Ambient Air Temperature For Storage   | -50...85 °C                  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 23.0 cm   |
| Package 1 Width              | 37.0 cm   |
| Package 1 Length             | 39.5 cm   |
| Package 1 Weight             | 11.231 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)