

Product data sheet

Specifications



Circuit breaker frame, MasterPact
NW10H1, 1000A, 65kA/440VAC
50/60Hz (Icu), 3 poles, fixed, without
control unit

48015

Main

Range	MasterPacT
Product Name	MasterPact NW
Circuit Breaker Name	MasterPact NW10H1
Product Or Component Type	Circuit breaker
Device Application	Power distribution protection
Poles Description	3P
Control Unit	Without control unit
[In] Rated Current	1000 A at 40 °C
Performance Type	H1 65 kA 440 V AC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Selectivity Category	Category B
Control Type	Push-button
Mounting Mode	Fixed

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	65 kA at 220/415 V AC 50/60 Hz
	65 kA at 440 V AC 50/60 Hz
	65 kA at 525 V AC 50/60 Hz
	65 kA at 690 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220/415 V AC 50/60 Hz
	65 kA at 440 V AC 50/60 Hz
	65 kA at 525 V AC 50/60 Hz
	65 kA at 690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	65 kA 1 s
	36 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	143 kA 220/415 V AC at 50/60 Hz
	143 kA 440 V AC at 50/60 Hz
	143 kA 525 V AC at 50/60 Hz
	143 kA 690 V AC at 50/60 Hz
Sensor Rating	400 A
	1000 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	70 W
Maximum Breaking Time	25 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Closing Response Time	70 ms
Mounting Support	Backplate Rails
Upside Connection	Front Rear
Downside Connection	Front Rear
Connection Pitch	115 mm
Mechanical Durability	12500 cycles without maintenance 25000 cycles with maintenance
Electrical Durability	10000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 AC-23A: 10000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-23A: 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3
Height	352 mm
Width	422 mm
Depth	297 mm
Net Weight	50 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2
Product Certifications	CE CCC EAC

Environment

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	4 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	29.5 cm
Package 1 Length	37.5 cm
Package 1 Weight	47.252 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov