

Product data sheet

Specifications

Thorsman - TML-TT20 - front cover - white - 2.55 m



5000013

Main

Range Of Product	Thorsman
Product Name	Thorsman TML
Product Or Component Type	Front cover
Trunking Material	Plastic
Quantity Per Set	Set of 20
Ambient Air Temperature For Operation	-20...60 °C

Complementary

Colour Tint	White
Fixing Mode	Snap-fitted
Material	PVC (polyvinyl chloride)

Environment

Ip Degree Of Protection	IP20
Length	2550 mm
Height	20 mm
Width	16 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	1.800 cm
Package 1 Length	255.000 cm
Package 1 Weight	230.000 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	1440
Package 2 Height	49.200 cm
Package 2 Width	120.000 cm
Package 2 Length	260.000 cm
Package 2 Weight	379.572 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations