

Product data sheet

Specifications

Thorsman - TEK-YH123 - external corner/front cover - 72 mm - white



5526520

Main

Range Of Product	Thorsman
Product Name	Thorsman TEK
Product Or Component Type	External corner
Provided Equipment	Front cover
Colour Tint	White (NCS 0401-Y62R)
Quantity Per Set	Set of 1

Complementary

Trunking Material	Plastic
Trunking Dimension	123 x 72 mm
Material	PVC (polyvinyl chloride)
Width	123 mm
Depth	72 mm

Environment

Quality Labels	CE
Standards	EN 50085-1:1997/A1 EN 50085-1:1998 KEMA 55A:1984 SS 424 10 02:1993
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.200 cm
Package 1 Width	28.400 cm
Package 1 Length	23.900 cm
Package 1 Weight	400.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations