


Product data sheet

Specifications



Thorsman - TEK-TSU161-3 - T-piece dropping - 72 mm - white RAL 9010

5532651

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

Main

Range Of Product	Thorsman
Product Name	Thorsman TEK
Product Or Component Type	T-piece
Trunking Dimension	161 x 72 mm
Trunking Material	Plastic
Direction Change Type	Downward
Colour Tint	White (RAL 9010)
Material	PVC (polyvinyl chloride)
Quantity Per Set	Set of 1

Complementary

Length	360 mm
Height	260 mm
Width	72 mm

Environment

Standards	KEMA 55A : 1984 EN 50085-1 : 1997/A1 : 1998 SS 424 10 02 : 1993 CE
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	36 cm
Package 1 Width	26 cm
Package 1 Length	7.2 cm
Package 1 Weight	1.1 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations