

Product data sheet

Specifications



substation - S54 - Sepam series 40

59786

⚠ Discontinued on: Jan 12, 2024

⚠ To be end-of-service on: Dec 31, 2030

⚠ Discontinued - Service only

Main

Relay Application	Substation
Range Of Product	Sepam series 40
Device Short Name	S54
Control And Monitoring Type	Latching/acknowledgement ANSI code: 86 Logic discrimination ANSI code: 68 (option) Switching of groups of settings Annunciation ANSI code: 30 Circuit breaker/contactors control ANSI code: 94/69 Logic equation editor 100 operators
Metering Type	Phase current I1, I2, I3 RMS, residual current I0 Demand current I1, I2, I3, peak demand current IM1, IM2, IM3 Voltage U21, U32, U13, V1, V2, V3, residual voltage V0 Frequency Positive sequence voltage Vd/rotation direction-negative sequence voltage Vi Active, reactive, apparent power P,Q,S-peak demand power PM, QM, power factor Calculated active and reactive energy (+/- W.h, +/- VAR.h) Active and reactive energy by pulse counting (+/- W.h, +/- VAR.h) (option)
Network And Machine Diagnosis Type	Unbalance ratio/negative sequence current Ii Disturbance recording Tripping context Fault locator 21FL Cable arcing fault detection Phase displacement
Switchgear Diagnosis Type	Cumulative breaking current Trip circuit supervision (option) Number of operations, operating time charging time (option) CT/VT supervision ANSI code: 60FL

Complementary

Type Of Measurement	Power factor Power (P,Q) Voltage Energy Current Peak demand power Frequency
Protection Type	Recloser (4 cycles) ANSI code: 79 (option) Breaker failure ANSI code: 50BF (1) Undervoltage protection ANSI code: 27/27S (2) Overvoltage protection ANSI code: 59 (2) Broken conductor ANSI code: 46BC (1) Phase overcurrent ANSI code: 50/51 (4) Earth fault/sensitive earth fault ANSI code: 50N/51N (4) Earth fault/sensitive earth fault ANSI code: 50G/51G (4) Negative sequence/unbalance ANSI code: 46 (2) Negative sequence overvoltage ANSI code: 47 (1)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communication Port Protocol	Measurement readout (option) : Modbus Remote indication and time tagging of events (option) : Modbus Remote control orders (option) : Modbus Remote protection setting (option) : Modbus Transfer of disturbance recording data (option) : Modbus
Input Output Max Capacity	10 inputs + 8 outputs
Communication Compatibility	Modbus TCP/IP Modbus RTU IEC 60870-5-103 IEC 61850 DNP3
User Machine Interface Type	Without Advanced Remote

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	10.0 cm
Package 1 Length	10.01 cm
Package 1 Weight	1.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	