

Bảng thông số sản phẩm

Thông số kỹ thuật



Motor circuit breaker, Easy TeSys Power, GZ1E, AC-3, 3P, 0.16..0.25A, thermal magnetic trip

GZ1E02

Main

Range	Easy TeSys
Range Of Product	Easy TeSys Power
Product Or Component Type	Circuit breaker
Device Short Name	GZ1E
Device Application	Motor
Trip Unit Technology	Thermal-magnetic
Suitability For Isolation	Yes conforming to IEC 60947-1 appendix 7.1.6
Colour	Grey (RAL 7011)

Complementary

Poles Description	3P
Network Type	AC
Utilisation Category	AC-3
Network Frequency	50/60 Hz conforming to IEC 60947-2
Mounting Mode	By screws By clips
Mounting Support	Rail
Mounting Position	Any position
Breaking Capacity	Icu: >= 100 kA at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 Icu: >= 100 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu: >= 100 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu: >= 100 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 Icu: >= 100 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 440 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 690 V AC 50/60 Hz conforming to IEC 60947-2
Control Type	Push-button
Thermal Protection Adjustment Range	0.16...0.25 A
Magnetic Tripping Current	2.4 A
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2
Power Dissipation	2.5 W (per pole)

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles for AC-3
Maximum Operating Rate	25 cyc/h
Connections - Terminals	Screw clamp terminals 2 1...6 mm² - cable stiffness: solid Screw clamp terminals 2 1.5...6 mm² - cable stiffness: flexible without cable end Screw clamp terminals 2 1...4 mm² - cable stiffness: flexible with cable end
Height	89 mm
Width	44.5 mm
Depth	78 mm
Net Weight	0.26 kg

Environment

Standards	IEC 60947-2 IEC 60947-4
Protective Treatment	TH
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1
Operating Altitude	2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	9.0 cm
Package 1 Length	4.6 cm
Package 1 Weight	220.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.643 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

 Mercury Free

 Rohs Exemption Information [Yes](#)

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information