


Product data sheet

Specifications



iPF65 modular surge arrester - 1 pole + N - 340V

A9L15684

 **Discontinued on:** Mar 31, 2022

 **Discontinued**

Main

Range Of Product	Acti9
Product Name	Acti9 iPF
Product Or Component Type	Surge arrester
Device Short Name	iPF
Device Application	Distribution
Standards	EN 61643-11 IEC 61643-11
Product Certifications	CE
Quality Labels	OVE NF KEMA-KEUR
Poles Description	1P + N
Remote Signalling	Without
Surge Arrester Type	Electrical distribution network
Earthing System	TN-S TT

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV + GDT
[Ue] Rated Operational Voltage	230 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 20 kA (L/PE) Common mode: 20 kA (N/PE) Differential mode: 20 kA (L/N)
[Imax] Maximum Discharge Current	Common mode: 65 kA L/PE Common mode: 65 kA N/PE Differential mode: 65 kA L/N
[Uc] Maximum Continuous Operating Voltage	Common mode: 340 V L/PE Common mode: 260 V N/PE Differential mode: 340 V L/N
Maximum [Up] Voltage Protection Level	Common mode <1.5 kV type 2 N/PE Differential mode <1.5 kV type 2 L/N
Disconnecter Device Type	Associated circuit breaker IC60N 50 A curve C - Icu 10 kA Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker NG125N 50 A curve C - Icu 25 kA Associated circuit breaker NG125H 50 A curve C - Icu 36 kA Associated circuit breaker NG125L 50 A curve C - Icu 50 kA
Mounting Mode	Clip-on (DIN rail)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

9 Mm Pitches	4
Height	81.4 mm
Width	36 mm
Depth	69 mm
Net Weight	0.21 kg
Colour	White (RAL 9003)
Connections - Terminals	Tunnel type terminal (downside) 2.5...35 mm² Tunnel type terminal (upside) 2.5...35 mm²
Tightening Torque	2.5 N.m

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	5...90 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	4 cm
Package 1 Length	8.1 cm
Package 1 Weight	0.237 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Plastic Parts Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins