


Product data sheet

Specifications



FR.PL.V.FIXED MOT.NS1600 SP

03701

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NS1250 - control: motor mechanism - vertical installation ComPact: fixed NS1600 - control: motor mechanism - vertical installation ComPact: fixed NS630b...1000 - control: motor mechanism - vertical installation
Poles Description	1 x 3P: mounting plate support: NS1250 vertical installation 1 x 4P: mounting plate support: NS1250 vertical installation 1 x 3P: mounting plate support: NS1600 vertical installation 1 x 4P: mounting plate support: NS1600 vertical installation 1 x 3P: mounting plate support: NS630b...1000 vertical installation 1 x 4P: mounting plate support: NS630b...1000 vertical installation
Operating Position	Vertical

Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm
Connection Position	Rear connection Front connection
Number Of Vertical Modules [50 Mm]	7
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	350 mm
Width	500 mm
Net Weight	1.52 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 front connection on Canalis 17
	650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 front connection on adaptor 14
	650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 front connection on Canalis 17
	650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 front connection on adaptor 14
	650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 3P 1 rear connection on adaptor 10
	650 mm 800 mm Prisma P cubicle ComPact NS1250 fixed motor mechanism vertical 4P 1 rear connection on adaptor 10
	650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 3P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 3P 1 front connection on adaptor 14
	650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 4P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 4P 1 front connection on adaptor 14
	650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 3P 1 rear connection on adaptor 10
	650 mm 800 mm Prisma P cubicle ComPact NS1600 fixed motor mechanism vertical 4P 1 rear connection on adaptor 10
	650 mm 400 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 3P 1 front connection on Canalis 17
	650 mm 800 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 3P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 3P 1 front connection on adaptor 12
	650 mm 400 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 4P 1 front connection on Canalis 17
	650 mm 800 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 4P 1 rear connection on Canalis 16
	650 mm 400 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 4P 1 front connection on adaptor 12
	650 mm 800 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 3P 1 rear connection on adaptor 10
	650 mm 800 mm Prisma P cubicle ComPact NS630b...1000 fixed motor mechanism vertical 4P 1 rear connection on adaptor 10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	35.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	1.550 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	39.000 cm
Package 2 Width	42.000 cm
Package 2 Length	52.000 cm
Package 2 Weight	23.660 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	60
Package 3 Height	95.000 cm
Package 3 Width	80.000 cm

Package 3 Length	120.000 cm
Package 3 Weight	94.640 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information