

Product data sheet

Specifications



discrete output module Modicon Quantum - 32 O solid state

140DDO35300C

⚠ Discontinued on: Dec 31, 2021

⚠ To be end-of-service on: Dec 31, 2029

⚠ Discontinued - Service only

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Dc discrete output module
Discrete Output Number	32

Complementary

Group Of Channels	4 groups of 8
Discrete Output Logic	Positive logic (source)
Addressing Requirement	2 output words
Discrete Output Voltage	24 V DC
Output Voltage Limits	19.2...30 V
Absolute Maximum Output	56 V for 1.3 s decaying pulse
Maximum Voltage Drop	<0.4 V 0.5 A
Maximum Load Current	16 A per module 4 A per group
Surge Current	5 A for 0.0005 s
Response Time	<= 1 ms at state 0 to state 1 <= 1 ms at state 1 to state 0
Maximum Leakage Current	0.4 mA 30 V
Load Inductance	$\text{Inductance(H)} = 0.5 / ((\text{current(A)})^2 \times (\text{switching frequency(Hz)}))$ 50 Hz
Fault Indication	Loss of field power Blown fuse
Associated Fuse Rating	3 A each point 5 A per group
Isolation Between Channels And Bus	1780 Vrms DC for 1 minute
Isolation Between Group	500 Vrms DC for 1 minute
Protection Type	Internal output protection by 5 A fuse per group
Power Dissipation	1.75 W + (0.4 V x total module load current)
Marking	CE
Local Signalling	1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault detected (F) 32 LEDs (green) for input status
Bus Current Requirement	330 mA
Module Format	Standard

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.45 kg
------------	---------

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Product Certifications	GL RINA BV GOST DNV FM Class 1 Division 2 C-Tick RMRS ABS
Standards	CSA C22.2 No 142 UL 508
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 80...2000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.3 cm
Package 1 Width	4.5 cm
Package 1 Length	31.2 cm
Package 1 Weight	465.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.08 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

24 Vdc Discrete Output Source Module

Wiring Diagram

