

Product data sheet

Specifications



residual current breaker with
overcurrent protection (RCBO),
Acti9 DPN N Vigi, 1P+N, 16A,
30mA, A-SI type, 6000A

A9N19634

Main

Circuit Breaker Application	Distribution
Range	Acti9
Product Or Component Type	Earth leakage circuit breaker
Product Name	DPN Vigi
Device Short Name	DPN N Vigi
Poles Description	1P + N
Neutral Position	Left
Number Of Protected Poles	1
[In] Rated Current	16 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Type	Type A-SI (Super Immunised)
Breaking Capacity	6000 A Icn at 230 V AC conforming to EN 61009
Utilisation Category	Category A

Complementary

Device Location In System	Outgoer
[Ue] Rated Operational Voltage	230 V AC
Magnetic Tripping Limit	5...10 x In
Residual Current Tripping Technology	Voltage independent
[Ics] Rated Service Breaking Capacity	6000 A at 230 V AC 50/60 Hz conforming to EN 61009
Limitation Class	3 conforming to EN 61009
[Ui] Rated Insulation Voltage	400 V AC conforming to EN 61009
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN 61009
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Support	35 mm DIN rail

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	77.5 mm
Net Weight	125 g
Embedding Depth	44 mm
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	20000 cycles conforming to IEC 61009
Connections - Terminals	Tunnel type terminals (top or bottom) 1...10 mm² flexible with ferrule Tunnel type terminals (top or bottom) 1...16 mm² rigid
Wire Stripping Length	15 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Integrated

Environment

Standards	EN/IEC 61009-1 EN/IEC 61009-2-1
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN 61009
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-30...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	4.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	209.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.000 cm
Package 2 Width	10.000 cm
Package 2 Length	25.500 cm
Package 2 Weight	1.317 kg
Unit Type Of Package 3	S03

Number Of Units In Package 3	54
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	12.250 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

Yes



Halogen Free Plastic Parts Product

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins