

Product data sheet

Specifications



auxiliary contact - 1 NO + 1 SD NC -
for P25M - 415 V - 2.2 A

21120

Main

Range Of Product	Acti9
Product Or Component Type	OC or fault contact
Device Short Name	NO and SD
Signal Contacts Composition	1 NO + 1 NC
9 Mm Pitches	1

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Height	89 mm
Width	18 mm
Depth	65 mm
Connections - Terminals	Clamp terminal2 cable(s) 1 mm² - flexible Clamp terminal2 cable(s) 2.5 mm² - flexible Clamp terminal2 cable(s) 1 mm² - rigid

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	NEMKO CEBEC DEMKO FIMKO SEMKO
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	6.6 cm
Package 1 Length	9.0 cm
Package 1 Weight	44.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.292 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
Eu Rohs Directive	<div>Compliant</div> <div>EU RoHS Declaration</div>
China Rohs Regulation	<div>China RoHS declaration</div> <div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div>
Weee	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>
Circularity Profile	<div>No need of specific recycling operations</div>