

Product data sheet

Specifications



auxiliary contact - 1 OC + 1 SD/OC -
380..415 V - 6 A

26929

⚠ Discontinued on: Jun 30, 2021

⚠ Discontinued

Main

| | |
|-----------------------------|--|
| Range Of Product | Multi9 |
| Product Or Component Type | Double OC or fault contact |
| Device Short Name | OF and OF or OF and SD |
| Signal Contacts Composition | 2 C/O |
| [In] Rated Current | DC-12 1 A at 130 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC AC-12 3 A at 415 V, AC 50/60 Hz AC-12 6 A at 240 V, AC 50/60 Hz |
| 9 Mm Pitches | 1 |

Complementary

| | |
|-------------------------|--|
| Mounting Mode | Fixed |
| Mounting Support | DIN rail |
| Height | 84 mm |
| Width | 9 mm |
| Depth | 73 mm |
| Connections - Terminals | Clamp terminal2 cable(s) 1.5 mm ² - flexible Clamp terminal2 cable(s) 1.5 mm ² - rigid Clamp terminal1 cable(s) 0.5...2.5 mm ² - flexible Clamp terminal1 cable(s) 0.5...2.5 mm ² - rigid |
| Wire Stripping Length | 9 mm |
| Tightening Torque | 1 N.m |

Environment

| | |
|---------------------------------------|-------------------------------------|
| Standards | EN/IEC 60947-5-1 |
| Product Certifications | LCIE ASEFA KEMA ASTA |
| Ip Degree Of Protection | IP20 conforming to EN/IEC 60947-5-1 |
| Pollution Degree | 3 conforming to EN/IEC 60947-5-1 |
| Tropicalisation | 2 conforming to EN/IEC 60947-5-1 |
| Relative Humidity | 95 % at 55 °C |
| Ambient Air Temperature For Operation | -25...50 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------------|-------------|
| Ambient Air Temperature For Storage | -40...85 °C |
|-------------------------------------|-------------|

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.2 cm |
| Package 1 Width | 8 cm |
| Package 1 Length | 9 cm |
| Package 1 Weight | 46 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |