

Product data sheet

Specifications



voltage release - MN - 48 V AC

26961

Main

Range Of Product	Multi9
Product Or Component Type	Undervoltage release
Device Short Name	MN
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC
Control Type	Standard
9 Mm Pitches	2

Complementary

Range Compatibility	Multi9 Multi9 C60 Multi9 Multi9 N40 Acti 9 Acti9 iDPN
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - Terminals	Clamp terminal - 1 cable(s) 2.5 mm² - flexible Clamp terminal - 1 cable(s) 2.5 mm² - rigid Clamp terminal - 2 cable(s) 1.5 mm² - flexible Clamp terminal - 2 cable(s) 1.5 mm² - rigid
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	ASEFA LCIE KEMA ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	2.4 cm
Package 1 Length	8 cm
Package 1 Weight	70 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8.5 cm
Package 2 Width	9 cm
Package 2 Length	26.5 cm
Package 2 Weight	628 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.139 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information