

Product data sheet

Specifications

Thorsman - TGB 12x0.7 - fixing band - hole Ø 2.5 mm - set of 1



2705110

Main

Range Of Product	Thorsman
Product Or Component Type	Fixing band
Device Short Name	TGB
Quantity Per Set	Set of 1
Type Of Packing	Plastic bag

Complementary

Material	Galvanised steel Cold-rolled steel
Surface Finish	Zinc coated PELD (polyethylene low density)
Hole Size	Ø 2.5 mm Ø 5 mm
Practical Load Capacity	1.2 kN
Width	12.7 mm
Thickness	0.7 mm
Length	10 m
Net Weight	0.534 kg

Environment

Ambient Air Temperature For Operation	-40...100 °C
---------------------------------------	--------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	14.100 cm
Package 1 Length	13.400 cm
Package 1 Weight	550.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations