

# Product data sheet

Specifications



## circuit breaker NG160H - TMD - 63 A - 4 poles 4d

28654

⚠ Discontinued on: Oct 10, 2020

⚠ Discontinued

### Main

Range Of Product	NG160
Product Or Component Type	Circuit breaker
Device Short Name	NG160H
Circuit Breaker Name	NG160H
Device Application	Distribution
Poles Description	4P
Protected Poles Description	4t
Network Type	AC
Network Frequency	50/60 Hz
[In] Rated Current	63 A at 40 °C
Breaking Capacity Code	H
Breaking Capacity	15 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	27 kA at 380/415 V AC 50/60 Hz 37.5 kA at 220/240 V AC 50/60 Hz 11.25 kA at 500 V AC 50/60 Hz 16.5 kA at 440 V AC 50/60 Hz
Suitability For Isolation	Yes
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	63 A
Protection Type	Overload protection (thermal) Short-circuit protection (magnetic)

### Complementary

Control Type	Toggle
Mounting Mode	Clipped
Mounting Support	35 mm symmetrical DIN rail
Upside Connection	Front
Downside Connection	Front
Connections - Terminals	Tunnel type terminals
Mechanical Durability	10000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	5000 cycles 440 V
Local Signalling	ON/OFF indication
Magnetic Tripping Current	800 A
Long Time Pick-Up Adjustment Type Ir	Fixed
Earth-Leakage Protection	Separate block
Height	120 mm
Width	120 mm
Depth	82.5 mm
Product Compatibility	Single terminal

## Environment

Standards	IEC 60947-3
-----------	-------------

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Certifications & Standards

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)