

Product data sheet

Specifications



earth-leakage module Compact Vigi
MH - 30..10000 mA - 200..440 V - 4
poles

29211

ⓘ Discontinued

Main

Range Of Product	NS100...250 NR100...250
Range	ComPact
Product Or Component Type	Earth leakage add-on block
Device Application	Wiring
Range Compatibility	ComPact Compact NR circuit breaker ComPact ComPact NS circuit breaker
Poles Description	4P
Protected Poles Description	4t
[In] Rated Current	160 A 100 A
Earth-Leakage Add-On Module Name	MH
Earth-Leakage Protection Class	Class A
Residual Earth-Leakage Sensitivity Adjustment Type	Adjustable 5 settings
[I _{ōn}] Residual Earth-Leakage Sensitive Adjustment	0.03...10 A
Residual Earth-Leakage Time Delay Adjustment Type	Adjustable
[Δt] Residual Earth-Leakage Time Delay Adjustment	310 ms 0 ms 150 ms 60 ms

Complementary

Network Type	AC
Network Frequency	50/60 Hz
Mounting Support	DIN rail
Electrical Connection To Mcb	By screws
[U _e] Rated Operational Voltage	220...440 V AC 50/60 Hz conforming to IEC 60947-2
Earth-Leakage Protection	With
Maximum Breaking Time	800 ms
Overvoltage Category	Class II
Height	140 mm
Width	236 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	86 mm
Net Weight	3.2 kg

Environment

Electrical Shock Protection Class	Class II
Standards	IEC 60947-2
Product Certifications	ASEFA LCIE ASTA KEMA

Contractual warranty

Warranty	18 months
----------	-----------