

# Product data sheet

Specifications



## MN undervoltage release, Compact NS 100 to 630, 220 VAC to 240 VAC 50/60 Hz, 208 VAC to 277 VAC 60 Hz

29407

! Discontinued

! Discontinued on: Sep 14, 2020

### Main

Range	ComPact
Range Of Product	NS100...250 NS400...630 DC NS100...250 DC NR400...630 NSF150...250 NR100...250 NB400...600 NS400...630 NS125E NSJ400...600
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	208...277 V AC 60 Hz 220...240 V AC 50/60 Hz
Range Compatibility	ComPact ComPact NS ComPact Compact NB ComPact Compact NR ComPact Compact NSF ComPact Compact NSJ

### Complementary

Operating Threshold	0.35...0.7 Un opening 0.85 Un closing
Response Time	< 50 ms
Supply Holding Power	< 5 VA
Auxiliary Connection Terminal	Screw terminal 0...1.5 mm <sup>2</sup>

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	5.8 cm
Package 1 Length	8.3 cm
Package 1 Weight	122 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Certifications & Standards

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---