

# Product data sheet

Specifications



## Vertical distribution block, Acti9 VDIS, 3P+N, 125A, 250/440VAC, 66 connection points

A9XPK714

### Main

|                           |   |
|---------------------------|---|
| Range                     | Acti9   |
| Product Name              | Acti9 VDIS  |
| Product Or Component Type | Vertical distribution block   |
| Range Compatibility       | Pragma<br>Prisma G<br>Prisma Pack 250<br>Prisma Pack 160<br>PrismaSeT S |

### Complementary

|  |  |
|--|--|
| Poles Description                      | 3P + N   |
| [In] Rated Current                     | 125 A  |
| [Ue] Rated Operational Voltage         | 250/440 V  |
| Network Type                           | AC   |
| Network Frequency                      | 50/60 Hz   |
| [Ui] Rated Insulation Voltage          | 500 V  |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV   |
| Number Of Terminal Blocks              | 1 with 66 outgoers   |
| Connections - Terminals                | Supply: tunnel type terminals10...35 mm²<br>Distribution: push-in spring terminals1.5...10 mm² (rigid)<br>Distribution: push-in spring terminals4...16 mm² (stranded)<br>Distribution: push-in spring terminals1.5...16 mm² (flexible)<br>Distribution: push-in spring terminals1.5...16 mm² (flexible with ferrule) |
| Distribution Block Outgoers            | 14 holes for per phase<br>24 holes for neutral   |
| Pollution Degree                       | 3  |
| Height                                 | 680 mm   |
| Depth                                  | 71.5 mm  |
| Width                                  | 40.5 mm  |
| Net Weight                             | 2.04 kg  |

### Environment

|                         |        |
|-------------------------|--------|
| Ip Degree Of Protection | IPxx B |
|-------------------------|--------|

### Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |            |
|------------------------------|------------|
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 5.300 cm   |
| Package 1 Width              | 9.500 cm   |
| Package 1 Length             | 73.000 cm  |
| Package 1 Weight             | 2.182 kg   |
| Unit Type Of Package 2       | P06        |
| Number Of Units In Package 2 | 54         |
| Package 2 Height             | 75.000 cm  |
| Package 2 Width              | 60.000 cm  |
| Package 2 Length             | 80.000 cm  |
| Package 2 Weight             | 132.000 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |