

# Product data sheet

Specifications



## Rack PDU 2G, Metered, ZeroU, 32A, 230V, Clipsal 56 series AS/NZ input plug, (36) C13 & (6) C19 outlets

AP8853X678

### Overview

Presentation	APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using StruxureWare software suite.
Lead Time	Special Order - Call for Quoted Lead Times

### Main

Pdu Type	Metered
Cord Length	3.00 m
Number Of Cables	1
Provided Equipment	Installation guide Rack mounting brackets Serial configuration cable

### Complementary

Input Voltage	200 V 208 V 230 V
Height	179.1 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.4 cm
Net Weight	6.93 kg
Mounting Location	Side
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	220...240 V
Max Line Current	32 A
Input Current Limits	32 A
Network Frequency	50/60 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Input Connectors	1 clipsal 32A 56P332
Total Number Of Outlets	36 IEC 60320 C13 6 IEC 60320 C19

## Environment

Product Certifications	VDE
Ambient Air Temperature For Operation	-5...45 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	200 cm
Package 1 Width	10.7 cm
Package 1 Length	16.2 cm
Package 1 Weight	8.56 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient   Take-back   Transparency   RoHS/REACH

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Lead Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation   [REACH Declaration](#)

Eu Rohs Directive   Compliant with Exemptions

Environmental Disclosure   [Product Environmental Profile](#)

Weee   The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile   [End of Life Information](#)