

Product data sheet

Specifications



1U 19" Black Modular Toolless Airflow Management Blanking Panel - Qty 200

AR8136BLK200

Overview

Presentation	Modular toolless 1U Airflow Management Blanking Panel to prevent air recirculation by occupying unused rack space (Qty. 200).
Lead Time	Usually in Stock

Main

Number Of Cables	1
Provided Equipment	User manual

Physical

Colour	Black
Height	4.5 cm
Width	48.3 cm
Depth	2.8 cm
Net Weight	0.09 kg
Mounting Preference	No preference
Mounting Mode	Rack-mounted

Conformance

Standards	EIA-310D
-----------	----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	44.5 cm
Package 1 Width	50.1 cm
Package 1 Length	52.7 cm
Package 1 Weight	25.856 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

✔ Take-Back Program Available

Well-being performance

✔ Reach Free Of Svhc

✔ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile