

Product data sheet

Specifications

trip unit - STR23SE OSN - 4 poles 3d



32443

! Discontinued

Main

Range	ComPact
Range Of Product	NR400...630
Product Or Component Type	Trip unit
Trip Unit Name	STR23SE OSN
Trip Unit Technology	Electronic
Range Compatibility	ComPact NS400 ComPact NS630
Device Application	Distribution
Number Of Poles	4P
Protected Poles Description	3t + 1.6 N 3t
Neutral Position	Left
Protection Type	for short time short-circuit protection for overload protection (long time) for instantaneous short-circuit protection
[Ue] Rated Operational Voltage	<= 525 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Motor Tripping Class	10
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 48 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.4...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	90...180 s at 1.5 x Ir 3.2...5 s at 7.2 x Ir 5...7.5 s at 6 x Ir
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 8 settings
[Isd] Short-Time Protection Pick-Up Adjustment Range	2...10 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Fixed
[Tsd] Short-Time Protection Delay Adjustment Range	0.04...0.06 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Display Type	LED
--------------	-----

Environment

Standards	IEC 60947-2
Product Certifications	ASEFA ASTA KEMA LCIE
Pollution Degree	3 conforming to IEC 60947
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Contractual warranty

Warranty	18 months
----------	-----------